


ITEM NUMBER	CATALOG NO.	Length (L)
50071271	BB048L6T38	6.00 [152]
50053117	BB048L12T38	12.00 [305]
50053118	BB048L18T38	18.00 [457]
50053119	BB048L24T38	24.00 [610]
50087064	BB048L30T38	30.00 [762]

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
D	07/27/2018	ADD BB048L30T38 TO DWG	49580	SC	



NOTES:

1. APPROXIMATE AMP RATING: 93A. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID, AND OTHER SERVICE CONDITIONS.
2. DIMENSIONS IN BRACKETS [ ] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.

3 ALL SIZES ARE LISTED TO UL 467 GROUNDING & BONDING EQUIPMENT STANDARDS.

TO ORDER BURNDY® PRODUCTS CALL		BRAID													
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: SEE TABLE CAT. NO: BB048L--T38 (TABLE)													
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		<table border="1"> <tr><td>DRAWN BY: M.RAJESHKUMAR</td><td>11/24/2014</td></tr> <tr><td>CHECKER: L.TROMBLEY</td><td>9/24/2017</td></tr> <tr><td>DSN APRVL: L.TROMBLEY</td><td>9/24/2017</td></tr> <tr><td>MFG APRVL: -</td><td>2/5/2015</td></tr> <tr><td>QA APRVL: B. POST</td><td>9/11/2017</td></tr> <tr><td>MKT APRVL: K.ROBICHEAU</td><td>9/10/2017</td></tr> </table>		DRAWN BY: M.RAJESHKUMAR	11/24/2014	CHECKER: L.TROMBLEY	9/24/2017	DSN APRVL: L.TROMBLEY	9/24/2017	MFG APRVL: -	2/5/2015	QA APRVL: B. POST	9/11/2017	MKT APRVL: K.ROBICHEAU	9/10/2017
DRAWN BY: M.RAJESHKUMAR	11/24/2014														
CHECKER: L.TROMBLEY	9/24/2017														
DSN APRVL: L.TROMBLEY	9/24/2017														
MFG APRVL: -	2/5/2015														
QA APRVL: B. POST	9/11/2017														
MKT APRVL: K.ROBICHEAU	9/10/2017														
FOR PRODUCT INFO: <a href="http://www.burndy.com">http://www.burndy.com</a>		PROJ #:	REV												
		MECHANICAL GROUNDING	50048729												
		SALES	D												
		Released	SHEET 1 OF 1												