



DRAWING# 50049480

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	09/22/2014	NEW DRAWING CREATED	37902	PB	DD

ITEM NO.	CATALOG NO.	LENGTH		
		L (IN)	L (FT)	L [mm]
25015482	BB300L36	36	3.0	[914]
25017633	BB300L48	48	4.0	[1219]
081029	BB300L120	120	10.0	[3048]
332747	BB300L144	144	12.0	[3658]
50096790	BB300L180	180	15.0	[4572]
332736	BB300L240	240	20.0	[6096]
3321AE	BB300L300	300	25.0	[7620]
25020036	BB300L360	360	30.0	[9144]
3320RX	BB300L600	600	50.0	[15240]
25016627	BB300L720	720	60.0	[18288]
332383	BB300L900	900	75.0	[22860]
25017261	BB300L1200	1200	100.0	[30480]
25003422	BB300L1320	1320	110.0	[33528]
001485	BB300L3000	3000	250.0	[76200]
10026414	BB300L3600	3600	300.0	[91440]
10081675	BB300L6000	6000	500.0	[152400]



BRAID
300 kcmil

NOTES:

1. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED AND ARE FOR REFERENCE ONLY.
2. MATERIAL:
TIN PLATED COPPER
3. FOR OTHER BRAID SIZES, REFERENCE DRAWING #10110676.
4. AVAILABLE IN OTHER LENGTHS UPON REQUEST.
5. LONG LENGTHS MAY NOT BE ONE CONTINUOUS PIECE.

TO ORDER BURNDY PRODUCTS CALL		BRAID	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: SEE TABLE	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: BB300L--(TABLE)	
FOR PRODUCT INFO: http://www.burndy.com		DRAWN BY: PARTHIBAN B 9/22/2014	
		CHECKER: L TROMBLEY 10/7/2014	
		DSN APRVL: L TROMBLEY 10/7/2014	
		MFG APRVL: --	
		QA APRVL: C LINDQUIST 10/8/2014	
		MKT APRVL: K ROBICHEAU 10/7/2014	
		PROD FAM: --	
		DRAWING NO	
		50049480	
		REV	
		A	
		SIZE	
		B	
		SHEET 1 OF 1	