


CATALOG NUMBER	ITEM NUMBER	DESCRIPTION	HOSE I.D.	LENGTH L
PT2990125QD	25003371	HIGH PRESSURE HOSE ASSEMBY (QUICK DISCONNECT TYPE)	1/4"	25' 0"
PT2990115QD	25003372	HIGH PRESSURE HOSE ASSEMBY (QUICK DISCONNECT TYPE)	1/4"	15' 0"
PT2990110QD	25003373	HIGH PRESSURE HOSE ASSEMBY (QUICK DISCONNECT TYPE)	1/4"	10' 0"
PT2990025QD	25003375	HIGH PRESSURE HOSE ASSEMBY (QUICK DISCONNECT TYPE)	3/16"	25' 0"
PT2990010QD	25003377	HIGH PRESSURE HOSE ASSEMBY (QUICK DISCONNECT TYPE)	3/16"	10' 0"
PT2990210	431213	HIGH PRESSURE HOSE ASSEMBY	3/16"	10' 0"
PT2990215	431214	HIGH PRESSURE HOSE ASSEMBY	3/16"	15' 0"
PT2990225	431215	HIGH PRESSURE HOSE ASSEMBY	3/16"	25' 0"

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	12/17/2012	SALES DRAWING CREATION	29949	PM	MB



NOTES:

1. MAXIMUM PRESSURE : 12,000 PSIG ± 120 PSIG.
- 2 DIM. ' L1 ' (APPROX. OVER ALL) IS EQUAL TO ' L ' (HOSE LENGTH) + 5.25 INCHES.
- 3 END CAPS ARE TO BE THREADED ON PRIOR TO SHIPPING.
- 4 END CAP IS INCLUDED WITH HALF BODY COUPLER.

TO ORDER BURNDY® PRODUCTS CALL		HIGH PRESSURE HOSE ASSEMBLY	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: SEE TABLE	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: SEE TABLE	
FOR PRODUCT INFO: http://www.burndy.com		DRAWN BY: PALANI M 12/17/2012	
		CHECKER: M CHIASSON 5/21/2013	
		DSN APRVL: M CHIASSON 5/21/2013	
		MFG APRVL: --	
		QA APRVL: --	
		MKT APRVL: D OWENS 4/9/2013	
		PROJ #: --	
		SIZE: B	
		DRAWING NO: 50016459	
		REV: A	
		SHEET 1 OF 1	