




WIRE SIZE (AWG)	STUD SIZE	CATALOG NUMBER	BULK CATALOG NUMBER	TAPE MOUNTED CATALOG NUMBER 2000/REEL	AS25036 DASH NO.	SAE CLASS #		C		K		L MAX.	N		T ±.01 [±.25]	Y MAX.	Z MIN.	MAX. WIRE INSUL. DIA. ACCOM.	WIRE STRIP LENGTH ±.03 [±.8]	COLOR CODE	INSTALLATION TOOLING (ONE CRIMP)
						1	2	MAX.	MIN.	MAX.	MIN.		MAX.	MIN.							
26-20 Str. and Sol.	2	YAE22G12BOX	YAE22G12	-	-	-	-	.26 [6.5]	.24 [6.2]	.10 [2.5]	.09 [2.3]	.73 [18.6]	.13 [3.3]	.12 [3.0]	.02 [.6]	.61 [15.6]	.22 [5.6]	.10 [2.5]	5/32" [4.0]	AMBER	M8ND [N14HET25V1]
		YAE22G18BOX	YAE22G18	YAE22G18M	143	-	X	.16 [3.9]	.14 [3.7]			.68 [17.4]	.08 [2.0]	.07 [1.8]							
	4	YAE22G16BOX	YAE22G16	YAE22G16M	144	-	X	.26 [6.5]	.24 [6.2]	.12 [3.0]	.11 [2.8]	.73 [18.6]	.13 [3.3]	.12 [3.0]							
	6	YAE22G13BOX	YAE22G13	YAE22G13M	145	-	X	.32 [8.3]	.30 [7.7]	.15 [3.8]	.14 [3.6]	.82 [20.7]	.16 [4.1]	.15 [3.9]							
	8	YAE22G14BOX	YAE22G14	-	146	-	X			.18 [4.5]	.16 [4.1]										
10	YAE22G15BOX	YAE22G15	-	147	-	X			.23 [5.8]	.19 [4.8]											

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	09/26/2018	NEW DRAWING CREATION	49942	BK	VS



**NOTES:**

1. TERMINAL: TIN PLATED COPPER
2. INSULATION: NYLON
3. DIMENSIONS IN BRACKETS [ ] ARE IN MILLIMETERS AND ARE FOR REFERENCE ONLY.
4. DIE SETS ARE LISTED IN BRACKETS [ ] AFTER THEIR RESPECTIVE TOOLS.
5. WIRE CONNECTOR:
  - 300V MAXIMUM
  - TEMPERATURE RATING OF INSULATING MATERIAL 105°C
  - FLAME RATING: UL746C GLOW WIRE TEST
6. MEETS REQUIREMENTS OF SAE-AS7928 (MAIN OFFICE CAGE CODE NUMBER: 1NJK8)

TO ORDER BURNDY® PRODUCTS CALL		INSULUG™	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: SEE TABLE	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: TYPE YAE-G	
FOR PRODUCT INFO: <a href="http://www.burndy.com">http://www.burndy.com</a>		DRAWN BY: K.BALAJI 26-09-2018 CHECKER: S.VENKATESAN 26-09-2018 DSN APRVL: K.CASTONGUAY 15-10-2018 MFG APRVL: -- QA APRVL: B.POST 01-10-2018 MKT APRVL: M.BAILLY 01-10-2018 PROD FAM: --	
		PROJECT #: -- DOCUMENT TYPE: SALES REL LEVEL: Released	
			REV: A