


REV	DATE	DESCRIPTION	ECO	BY	C'HK.
C	01/27/2020	UPDATED AS PER MARKUP	52903	SS	YR

MEDIUM VOLTAGE SLEEVES -BARE CONCENTRIC 5 kV					
BURNDY SLEEVE CATALOG NUMBER 	BURNDY SLEEVE ITEM NUMBER	SLEEVE RANGE	INSULATION DIAMETER RANGE	INSULATION DIAMETER (PRESHRINK)	STANDARD PACKAGE QUANTITY
CSB520420	50104755	4 - 2/0	0.51-0.64 [13-16.2]	0.91 [23]	1
CSB52120250	50104756	2/0 - 250	0.64-0.79 [16.2-20.2]	1.10 [28]	
CSB522250500	50104757	250 - 500	0.79-1.04 [20-26.4]	1.42 [36]	
CSB5235001000	50104758	500 - 1000	1.02-1.45 [26-36.8]	1.77 [45]	



NOTES:

1. MATERIAL: SILICON RUBBER

 INCLUDES : (JOINT, SEALANT PACK, SEALANT PACK, CONSTANT FORCE SPRING, PRODUCT INSTALLATION GUIDE, VIOLET PVC TAPE).


3. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED AND ARE FOR REFERENCE ONLY.

4. CONFORMS TO IEEE-48-2009, CLASS 1 STANDARDS.

5. CONFORMS TO ISO/IEC 17025 STANDARDS.

6. RUS APPROVED.

7. REPORT # HVS CST 181207.

TO ORDER BURNDY® PRODUCTS CALL		CSJ20 SPLICE													
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: SEE TABLE													
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: SEE TABLE													
FOR PRODUCT INFO: http://www.burndy.com		<table border="1"> <tr> <td>DRAWN BY: R. BABU</td> <td>11/22/2018</td> </tr> <tr> <td>CHECKER: K. JAYAVIGNESH</td> <td>8/30/2019</td> </tr> <tr> <td>DSN APRVL: --</td> <td>12/30/1899</td> </tr> <tr> <td>MFG APRVL: --</td> <td>12/30/1899</td> </tr> <tr> <td>QA APRVL: --</td> <td>12/30/1899</td> </tr> <tr> <td>MKT APRVL: --</td> <td>12/30/1899</td> </tr> </table>		DRAWN BY: R. BABU	11/22/2018	CHECKER: K. JAYAVIGNESH	8/30/2019	DSN APRVL: --	12/30/1899	MFG APRVL: --	12/30/1899	QA APRVL: --	12/30/1899	MKT APRVL: --	12/30/1899
DRAWN BY: R. BABU	11/22/2018														
CHECKER: K. JAYAVIGNESH	8/30/2019														
DSN APRVL: --	12/30/1899														
MFG APRVL: --	12/30/1899														
QA APRVL: --	12/30/1899														
MKT APRVL: --	12/30/1899														
<table border="1"> <tr> <td>PROJECT #:</td> <td>SIZE</td> <td>DRAWING NO</td> <td>REV</td> </tr> <tr> <td>DOCUMENT TYPE: Sales</td> <td>B</td> <td>50095758</td> <td>C</td> </tr> <tr> <td>REL LEVEL: Released</td> <td></td> <td>SHEET 1 OF 3</td> <td></td> </tr> </table>		PROJECT #:	SIZE	DRAWING NO	REV	DOCUMENT TYPE: Sales	B	50095758	C	REL LEVEL: Released		SHEET 1 OF 3			
PROJECT #:	SIZE	DRAWING NO	REV												
DOCUMENT TYPE: Sales	B	50095758	C												
REL LEVEL: Released		SHEET 1 OF 3													

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
C	01/27/2020	UPDATED AS PER MARKUP	52903	SS	YR

MEDIUM VOLTAGE SLEEVES - JACKETED CONCENTRIC 8 KV					
BURNDY SLEEVE CATALOG NUMBER ²	BURNDY SLEEVE ITEM NUMBER	SLEEVE RANGE	INSULATION DIAMETER RANGE	INSULATION DIAMETER (PRESHRINK)	STANDARD PACKAGE QUANTITY
CSJ820410	50104759	4 - 1/0	0.51-0.64 [13-16.2]	0.91 [23]	1
CSJ8211040	50104760	1/0 - 4/0	0.64-0.79 [16.2-20.2]	1.10 [28]	
CSJ82240500	50104761	4/0 - 500	0.79-1.04 [20-26.4]	1.42 [36]	
CSJ8235001000	50104762	500 - 1000	1.02-1.45 [26-36.8]	1.77 [45]	

NOTES:

1. MATERIAL: SILICON RUBBER

² INCLUDES : (JACKET, JOINT, SEALANT PACK, SEALANT PACK, SHIELD/GROUND KIT, PRODUCT INSTALLATION GUIDE).

3. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED AND ARE FOR REFERENCE ONLY.

4. CONFORMS TO IEEE-48-2009, CLASS 1 STANDARDS.

5. CONFORMS TO ISO/IEC 17025 STANDARDS.

6. RUS APPROVED.

7. REPORT # HVS CST 181207.



TO ORDER BURNDY® PRODUCTS CALL		CSJ20 SPLICE													
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: SEE TABLE													
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: SEE TABLE													
FOR PRODUCT INFO: http://www.burndy.com		<table border="1"> <tr> <td>DRAWN BY: R. BABU</td> <td>11/22/2018</td> </tr> <tr> <td>CHECKER: K. JAYAVIGNESH</td> <td>8/30/2019</td> </tr> <tr> <td>DSN APRVL: --</td> <td>12/30/1899</td> </tr> <tr> <td>MFG APRVL: --</td> <td>12/30/1899</td> </tr> <tr> <td>QA APRVL: --</td> <td>12/30/1899</td> </tr> <tr> <td>MKT APRVL: --</td> <td>12/30/1899</td> </tr> </table>		DRAWN BY: R. BABU	11/22/2018	CHECKER: K. JAYAVIGNESH	8/30/2019	DSN APRVL: --	12/30/1899	MFG APRVL: --	12/30/1899	QA APRVL: --	12/30/1899	MKT APRVL: --	12/30/1899
DRAWN BY: R. BABU	11/22/2018														
CHECKER: K. JAYAVIGNESH	8/30/2019														
DSN APRVL: --	12/30/1899														
MFG APRVL: --	12/30/1899														
QA APRVL: --	12/30/1899														
MKT APRVL: --	12/30/1899														
PROJ #: --		DRAWING NO													
DOCUMENT TYPE: Sales		50095758													
REL LEVEL: Released		SHEET 2 OF 3													
		REV													
		C													

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
C	01/27/2020	UPDATED AS PER MARKUP	52903	SS	YR

MEDIUM VOLTAGE SLEEVES - JACKETED CONCENTRIC 15 kV					
BURNDY SLEEVE CATALOG NUMBER	BURNDY SLEEVE ITEM NUMBER	SLEEVE RANGE	INSULATION DIAMETER RANGE	INSULATION DIAMETER (PRESHRINK)	STANDARD PACKAGE QUANTITY
CSJ15202	50104763	2	0.51-0.64 [13-16.2]	0.91 [23]	1
CSJ1521210	50104764	2 - 1/0	0.64-0.79 [16.2-20.2]	1.10 [28]	
CSJ152210350	50104765	1/0 - 350	0.79-1.04 [20-26.4]	1.42 [36]	
CSJ1523500750	50104766	500 - 750	1.02-1.45 [26-36.8]	1.77 [45]	
CSJ15247501000	50104767	750 - 1000	1.45-1.77 [36.8-45]	2.28 [58]	

NOTES:

1. MATERIAL: SILICON RUBBER
2. INCLUDES : (JACKET, JOINT, SEALANT PACK, SHIELD/GROUND KIT, PRODUCT INSTALLATION GUIDE).
3. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED AND ARE FOR REFERENCE ONLY.
4. CONFORMS TO IEEE-48-2009, CLASS 1 STANDARDS.
5. CONFORMS TO ISO/IEC 17025 STANDARDS.
6. RUS APPROVED.
7. REPORT # HVS CST 181207.



TO ORDER BURNDY® PRODUCTS CALL
 UNITED STATES
 1-800-346-4175 (LONDONDERRY, NH)
 CANADA:
 1-800-361-6975 (QUEBEC)
 1-800-387-6487 (ALL OTHER PROVINCES)
 FOR PRODUCT INFO: <http://www.burndy.com>

CSJ20 SPLICE	
ITEM NO: SEE TABLE	
CAT. NO: SEE TABLE	
DRAWN BY: R. BABU	11/22/2018
CHECKER: K. JAYAVIGNESH	8/30/2019
DSN APRVL: --	12/30/1899
MFG APRVL: --	12/30/1899
QA APRVL: --	12/30/1899
MKT APRVL: --	12/30/1899
PROD FAM:	DRAWING NO
PROJECT #: --	SIZE
DOCUMENT TYPE: Sales	50095758
REL LEVEL: Released	B
	SHEET 3 OF 3
	REV
	C

