



EDGE CLIP WITH CABLE TIE (ACC-ECT SERIES)

PART NO.	CATALOG NO.	LENGTH (L)	NYLON CLIP & TIE MATERIAL	MAX BUNDLE DIA.	TENSILE STRENGTH	STYLE
50100742	ACC-ECTA68	200 mm [7.87 in]	UV RESISTANT, HEAT STABILIZED NYLON 6/6	49.5 mm [1.95 in]	23 kg [50 lb]	A
50101403	ACC-ECTA611	280 mm [11.02 in]	UV RESISTANT, HEAT STABILIZED NYLON 6/6	74.8 mm [2.95 in]	23 kg [50 lb]	A
50101404	ACC-ECTA614	360 mm [14.17 in]	UV RESISTANT, HEAT STABILIZED NYLON 6/6	100 mm [3.94 in]	23 kg [50 lb]	A
50101405	ACC-ECTA128	200 mm [7.87 in]	UV RESISTANT NYLON 12	49.5 mm [1.95 in]	23 kg [50 lb]	A
50101406	ACC-ECTA1211	280 mm [11.02 in]	UV RESISTANT NYLON 12	74.8 mm [2.95 in]	23 kg [50 lb]	A
50101407	ACC-ECTA1214	360 mm [14.17 in]	UV RESISTANT NYLON 12	100 mm [3.94 in]	23 kg [50 lb]	A
50101408	ACC-ECTB68	200 mm [7.87 in]	UV RESISTANT, HEAT STABILIZED NYLON 6/6	49.5 mm [1.95 in]	23 kg [50 lb]	B
50101409	ACC-ECTB611	280 mm [11.02 in]	UV RESISTANT, HEAT STABILIZED NYLON 6/6	74.8 mm [2.95 in]	23 kg [50 lb]	B
50101410	ACC-ECTB614	360 mm [14.17 in]	UV RESISTANT, HEAT STABILIZED NYLON 6/6	100 mm [3.94 in]	23 kg [50 lb]	B
50101411	ACC-ECTB128	200 mm [7.87 in]	UV RESISTANT NYLON 12	49.5 mm [1.95 in]	23 kg [50 lb]	B
50101412	ACC-ECTB1211	280 mm [11.02 in]	UV RESISTANT NYLON 12	74.8 mm [2.95 in]	23 kg [50 lb]	B
50101413	ACC-ECTB1214	360 mm [14.17 in]	UV RESISTANT NYLON 12	100 mm [3.94 in]	23 kg [50 lb]	B


REV	DATE	DESCRIPTION	EC	BY	C'H'K.
D	05-16-2023	DRAWING UPDATE	230518030343	TM	EM



Style A




Style B



EDGE CLIP COMPARTMENT



3D VIEW



NOTES:

- DIMENSIONS IN BRACKETS [] ARE IN INCHES ROUNDED OFF TO THE NEAREST TENTH, UNLESS OTHERWISE SPECIFIED AND ARE FOR REFERENCE ONLY.
- ALLOWS A CABLE TIE TO BE ROUTED IN BOTH LANDSCAPE (ON THE HORIZONTAL PORTION OF MODULE FRAME - STYLE B) AND PORTRAIT (ON THE VERTICAL PORTION OF MODULE FRAME - STYLE A) ORIENTATIONS.
- FLANGE THICKNESS RANGE: 1.3mm - 3.0mm
- LISTED TO UL62275

TO ORDER BURNDY® PRODUCTS CALL
 UNITED STATES
 1-800-346-4175 (LONDONDERRY, NH)
 CANADA:
 1-800-387-6487
 FOR PRODUCT INFO: <http://www.burndy.com>

EDGE CLIP WITH CABLE TIE		DRAWING NO	REV
ITEM NO: (SEE TABLE)		50100741	D
CAT. NO: ACC-ECTAXX & ACC-ECTBXX (SEE TABLE)		SHEET 1 OF 1	
DRAWN BY: K.NAUGLER	06-18-2019		
CHECKER: E.MARTIN	06-22-2023		
DSN APRVL: E.MARTIN	06-22-2023		
MFG APRVL: V.PETROVSKY	08-07-2023		
QA APRVL: J.BRODEUR	01-30-2023		
MKT APRVL: S.PARSONS	02-03-2023		
PROD FAM: WILEY	SIZE: B		
PROJECT #:	REL LEVEL: Released		