



PART NO.	(IT.#14) TOTAL QTY.	AMPS	(IT.#30, BOLT) PART NO.
<b>632576</b>	3	3000 OGE NOMINAL	TR92138124 1.5"
<b>63257600</b>	9	6000 OGE NOMINAL	TR92138132 2.0"
<b>63257601</b>	3	2000	TR92138124 1.5"
<b>63257602</b>	6	FULL 3000/OGE 5000	TR92138132 2.0"
<b>63257603</b>	9	FULL 4000	TR92138132 2.0"

ITEM	QTY	PART#	DESCRIPTION	MATERIAL
1	1	63489704	BASE FRAME WELDM'T	#12GA HRPO
2	2	63493405	DOOR FRAME WELDM'T	#12GA HRPO
3	2	63494005	DOOR/WELDM'T	#12GA HRPO
4	1	63493905	COVER / WELDM'T	#12GA HRPO
5	2	63490106	SIDE PANEL / WELDM'T	#12GA HRPO
6	2	63440905	RECESSED LOCK ASM.-PLAIN	(W/HEX)
7	4	63454714	DOOR ROD 20.562"	#304 SST
8	4	63200703	LIFTING DEVICE	#10GA HRPO
9	2	632018	DOOR HOLDER ROD	3/8" ROD
LOOSE-10	2	63273010	ANGLE - CHANNEL SUPPORT	#11GA HRPO
LOOSE-11	3	63273000	ANGLE - BUS SUPPORT	#11GA HRPO
LOOSE-12	2	63272905	CHANNEL - BUS SUPPORT	#12GA HRPO
TRINETICS-13	6	62200601	BUS SUP'T INSULATOR	RED FIBRGLS
TRINETICS-14	SEE TABLE	632785	PHASE BUS (3000 AMP)	.25 COPPER
LOOSE-15	2	632732	BRACKET - GROUND BUS	#12GA HRPO
TRINETICS-16	1	632786	GROUND BUS	.25 COPPER
LOOSE-17	2	63213504	UNISTRUT CHANNEL - 40.75"	#12GA HRPO
LOOSE-18	8	61209803	3/8-16 UNISTRUT NUT	S.S.
19	4	TR92250906	1/4-20 NYLOCK HEX NUT	S.S.
20	8	TR92600805	1/4 FLAT WASHER	S.S.
21	8	TR92620501	1/4 LOCK WASHER	S.S.
22	8	TR92250606	1/4-20 HEX NUT	S.S.
23	16	TR92099116	3/8-16 x 1" CARRIAGE BOLT	S.S.
24	45	TR92601005	3/8 FLAT WASHER	S.S.
25	36	TR92620701	3/8 LOCK WASHER	S.S.
26	36	TR92290604	3/8-16 HEX NUT	SIL.BRONZE
27	12	TR92098116	3/8-16 x 1.0 HHCS	S.S.
28	2	612124	3/8 PALNUT	S.S.
TRINETICS-29	12	TR92138116	1/2-13 x 1" HHCS	S.S.
TRINETICS-30	9	SEE TABLE	1/2-13 x 1.5" or 2" HHCS	S.S.
TRINETICS-31	30	TR92601305	1/2 FLAT WASHER	S.S.
TRINETICS-32	30	TR92620901	1/2 LOCK WASHER	S.S.
TRINETICS-33	9	TR92320606	1/2-13 HEX NUT	S.S.
34	4	TR92602105	5/8 FLAT WASHER	S.S.
35	4	TR92148112	5/8-11 x .75 HHCS	S.S.
36	AR	617055	MUNSELL GREEN POWDER	PAINT

THIS IS A CAD DRAWING. DO NOT MAKE MANUAL CHANGES!

08	65961	CLV	04/08/05
07	64392	CLV	10/04/01
06	64356	PST	09/05/01
05	64035	CLV	12/12/00
4	-	MD	03/07/91
3	1634	VH	11/18/88
2	1407	MS	04/18/88
1	1325	VH	12/16/87
REV	ERN	BY	DATE

(APPROVAL No. P311)

TOL. UNLESS NOTED  
 X ±.06  
 XX ±.03  
 XXX ±.015  
 ANGLES ±1°  
 FLATS ±.005

THIRD ANGLE PROJECTION

THIS DRAWING AND ALL INFORMATION THEREON IS THE SOLE PROPERTY OF TRINETICS. IT MUST NOT BE COPIED, REPRODUCED OR SUBMITTED TO OTHERS WITHOUT WRITTEN AUTHORIZATION. ALL REPRODUCTIONS ARE SUBJECT TO RETURN ON DEMAND. ALL DIMENSIONS ARE IN INCHES UNLESS OTHERWISE SPECIFIED.

TRINETICS

#12 GA (.1046) HRPO

SEC. MULTI-CONNECTION

SCALE 11/64

DATE 9/6/00

DRAWN BY VISSER

WEIGHT

SIZE FAMILY ID D C305

SHEET 1 OF 1

CURRENT ERN 65961

REV 008

PART NUMBER 632576 THRU 03