


DRAWING# 50049474				
ITEM NO.	CATALOG NO.	LENGTH		
		L (IN)	L (FT)	L [mm]
332798	BB024L12	12	1.0	[305]
10109682	BB024L18	18	1.5	[457]
10112863	BB024L24	24	2.0	[610]
50100930	BB024L36	36	3.0	[915]
25021131	BB024L60	60	5.0	[1524]
10027017	BB024L72	72	6.0	[1829]
25019024	BB024L108	108	9.0	[2743]
25016624	BB024L120	120	10.0	[3048]
000995	BB024L180	180	15.0	[4572]
33215U	BB024L240	240	20.0	[6096]
25017985	BB024L300	300	25.0	[7620]
25015222	BB024L325	325	27.1	[8255]
332726	BB024L480	480	40.0	[12192]
332361	BB024L600	600	50.0	[15240]
332925	BB024L1200	1200	100.0	[30480]
50094348	BB024L1800	1800	150.0	[45720]
10006817	BB024L2400	2400	200.0	[60960]
332410	BB024L3000	3000	250.0	[76200]
332553	BB024L6000	6000	500	[152400]
25017777	BB024L7200	7200	600.0	[182880]
50094348	BB024L1800	1800	150.0	[45720]

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
B	06/14/2019	FOCUS REQUEST FPN1906042	49825	JL	BE



NOTES:

1. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED AND ARE FOR REFERENCE ONLY.
2. MATERIAL:
TIN PLATED COPPER
3. FOR OTHER BRAID SIZES, REFERENCE DRAWING #10110676.
4. AVAILABLE IN OTHER LENGTHS UPON REQUEST.
5. LONG LENGTHS MAY NOT BE ONE CONTINUOUS PIECE.

TO ORDER BURNDY® PRODUCTS CALL		BRAID	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: SEE TABLE	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: BB024L--(TABLE)	
FOR PRODUCT INFO: http://www.burndy.com		DRAWN BY: PARTHIBAN B 9/22/2014	
		CHECKER: L TROMBLEY 10/6/2014	
		DSN APRVL: L TROMBLEY 10/6/2014	
		MFG APRVL:	
		QA APRVL: C LINDQUIST 10/7/2014	
		MKT APRVL: K ROBICHEAU 10/6/2014	
		PROD FAM: CM&R COMPRESSION	
		DRAWING NO	
		50049474	
		REV	
		B	
		SHEET 1 OF 1	