

CATALOG #	DESCRIPTION	CHARGER VOLTS	CHARGER ITEM #
PAT500SJ68L5	PAT500SJ68L5 WITH 120V CHARGER	120	30001520
PAT500SJ66L5	PAT500SJ66L5 WITH 120V CHARGER	120	30001520
PAT500SJ6L5	PAT500SJ6L5 WITH 120V CHARGER	120	30001520
PAT500SJ68L5DC	PAT500SJ68L5 WITH DC CHARGER	12/24	30001523
PAT500SJ66L5DC	PAT500SJ66L5 WITH DC CHARGER	12/24	30001523
PAT500SJ6L5DC	PAT500SJ6L5 WITH DC CHARGER	12/24	30001523
PAT500SJ68L5LCB	PAT500SJ68L5 LESS CHARGER & BATTERY	N/A	N/A
PAT500SJ66L5LCB	PAT500SJ66L5 LESS CHARGER & BATTERY	N/A	N/A
PAT500SJ6L5LCB	PAT500SJ6L5 LESS CHARGER & BATTERY	N/A	N/A
PAT500SJCUTL5	PAT500SJCUTL5 WITH 120V CHARGER	120	30001520
PAT500SJCUTL5DC	PAT500SJCUTL5 WITH DC CHARGER	12/24	30001523
PAT500SJCUTL5LCB	PAT500SJCUTL5 LESS CHARGER & BATTERY	N/A	N/A
PAT500SJ6L5CUTKITI	CRMP,6T,OP-HD (BG, D3) SCR,L5, W ACSR CUTTER	120	30001520
PAT500SJ68L5CUTKITI	CRMP,6T,OP-HD (O, D3) SCR,L5, W ACSR CUTTER	120	30001520

SPECIFICATIONS:

OUTPUT FORCE: 6 TONS (5.4 METRIC TONS)
 TOOL WEIGHT WITH BATTERY: 11.0 LBS (4.9 kg)
 LENGTH: 16.8 IN (42.6 cm)
 WIDTH: 2.9 IN (7.3 cm)
 HEIGHT: 13.4 IN (34.0 cm)
 OPERATING VOLTAGE: 18V-DC
 RECHARGE TIME: 45 MINUTES

FEATURES


- REFINED HYDRAULIC SYSTEM FOR ULTRA PERFORMANCE, SPEED AND RELIABILITY.
- FIELD PROVEN ELECTRONICS FOR ULTIMATE RELIABILITY IN THE HARSHTEST ENVIRONMENTS.
- OVERMOLDED HANDLE FOR COMFORT AND IMPROVED GRIP; ALLOWS FOR ONE HANDED OPERATION FOR ADVANCE RETRACT AND HOLD.
- FORCED AIR COOLING FAN COOLS THE BATTERY BY FORCING COOL AIR THROUGH THE BATTERY'S BUILT IN AIR VENTS.
- 6 TON OUTPUT FORCE.
- STATE OF THE ART CRIMPING HEAD DESIGN, 180° HEAD ROTATION LETS USER GET INTO TIGHT AREAS EASIER.
- AUDIBLE "POP OFF" INDICATES PROPERLY COMPLETED CRIMPS.
- ERGONOMICALLY BALANCED TOOL DESIGN EASES OPERATION AND HELPS LESSEN FATIGUE.
- DURABLE HIGH IMPACT FORMED CARRYING CASE PROVIDES SUPERIOR PROTECTION AND STORES ALL ACCESSORIES.
- 5 YEAR LIMITED WARRANTY ON THE TOOL.
- 3 YEAR LIMITED WARRANTY ON THE BATTERY & CHARGER.

BENEFITS


- VERSATILE TOOL HEAD POSITIONING LETS USER GET INTO TIGHT AREAS.
- LESS DOWN TIME DUE TO HIGH CAPACITY, HIGH VOLTAGE 18 VOLT LITHIUM ION BATTERY.
- ASSURES PROPER CRIMPS WITH AUDIBLE INDICATOR, LEAVING NO DOUBT FOR TOOL USER.
- SMOOTHER, QUIETER, MORE EFFICIENT TOOL OPERATION.
- MAKITA 18 VOLT LITHIUM-ION BATTERIES PROVIDE 2.5 TIMES MORE CHARGE/DISCHARGE CYCLES THAN TRADITIONAL Ni-Cd BATTERIES AND PROVIDE 430% MORE LIFETIME WORK.
- MAKITA CHARGER CONTROLS CURRENT, VOLTAGE AND TEMPERATURE TO MAXIMIZE BATTERY LIFE.

NOTES:

1. TOOL ACCEPTS 18V MAKITA LITHIUM-ION BATTERIES, BL SERIES, OF SIZE 2.0 AHR AND GREATER IF THE PLASTIC BATTERY CLIP IN THE TOOL HAS A "STAR" MOLDED INTO IT. THE "STAR" IDENTIFIES ACCEPTANCE OF THE BL SERIES BATTERIES.
2. FOR TOOLS WHICH DO NOT HAVE A "STAR" MOLDED INTO THE PLASTIC BATTERY CLIP, USE IS LIMITED TO THE BL1830 (3.0 AHR) BATTERY. FORCING ANY OTHER BATTERY INTO THIS TOOL WILL VOID THE WARRANTY.



REV.	DATE	DESCRIPTION	ECO	BY	C'H'K.
D	2019-11-18 00:00:00 EST	DRAWING RELEASED	52427	TRF	CMT



*** BILL OF MATERIAL ***

PT NO.	CATALOG NO.	QTY	DESCRIPTION
1	PATCASEL1	1	CASE, TOOL PATRIOT LITHIUM ION
2	PATCHGRL1	1	CHARGER, BATTERY LITHIUM ION
3	PT208620	1	LANYARD
4	BAT18V5AHL1	2	BATTERY, MAKITA 18V LI-ION 5.0 AH MAKITA P/N BL1850B
5	PAT500SJOM1	1	SOMI, PAT500SJ
6	PT20443801	1	WARRANTY CARD
7	LIMSDS	1	SDS, LITHIUM ION BATTERY

TO ORDER BURNDY® PRODUCTS CALL		Patriot 500 Scissor Jaw Tool															
UNITED STATES: 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: SEE TABLE															
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: SEE TABLE															
FOR PRODUCT INFO: http://www.burndy.com		<table border="1"> <tr> <td>DRAWN BY: T. FAUCHER</td> <td>08/17/2016</td> <td rowspan="6" style="text-align: center; vertical-align: middle;">BURNDY</td> <td rowspan="6" style="text-align: right; vertical-align: middle;">SCALE: 5:32</td> </tr> <tr> <td>CHECKER: M. CHIASSON</td> <td>08/18/2016</td> </tr> <tr> <td>DSN APPVL: M. CHIASSON</td> <td>08/19/2016</td> </tr> <tr> <td>MFG APPVL: C. TORREY</td> <td>08/19/2016</td> </tr> <tr> <td>QA APPVL: C. LINDQUIST</td> <td>08/19/2016</td> </tr> <tr> <td>MKT APPVL: P. SILVA</td> <td>08/19/2016</td> </tr> </table>		DRAWN BY: T. FAUCHER	08/17/2016	BURNDY	SCALE: 5:32	CHECKER: M. CHIASSON	08/18/2016	DSN APPVL: M. CHIASSON	08/19/2016	MFG APPVL: C. TORREY	08/19/2016	QA APPVL: C. LINDQUIST	08/19/2016	MKT APPVL: P. SILVA	08/19/2016
DRAWN BY: T. FAUCHER	08/17/2016	BURNDY	SCALE: 5:32														
CHECKER: M. CHIASSON	08/18/2016																
DSN APPVL: M. CHIASSON	08/19/2016																
MFG APPVL: C. TORREY	08/19/2016																
QA APPVL: C. LINDQUIST	08/19/2016																
MKT APPVL: P. SILVA	08/19/2016																
<table border="1"> <tr> <td>PROD FAM: TOOLS, BATTERY</td> <td>DRAWING NO</td> <td>REV</td> </tr> <tr> <td>PROJECT #: --</td> <td>50068040</td> <td>D</td> </tr> <tr> <td>DOCUMENT TYPE: Sales</td> <td>SIZE</td> <td></td> </tr> <tr> <td>REL LEVEL: Released</td> <td>B</td> <td></td> </tr> </table>		PROD FAM: TOOLS, BATTERY	DRAWING NO	REV	PROJECT #: --	50068040	D	DOCUMENT TYPE: Sales	SIZE		REL LEVEL: Released	B		SHEET 1 OF 1			
PROD FAM: TOOLS, BATTERY	DRAWING NO	REV															
PROJECT #: --	50068040	D															
DOCUMENT TYPE: Sales	SIZE																
REL LEVEL: Released	B																