




PART NO	CATALOG NO.	QTY	DESCRIPTION	WIRE SIZE	STUD SIZE
1	MRE1022NV	1	MECHANICAL RATCHET TOOL	--	--
2	PTV18	100	VINYL PIN TERMINAL	22-18 AWG	--
3	PTV10	100	VINYL PIN TERMINAL	12-10 AWG	--
4	PTV14	100	VINYL PIN TERMINAL	16-14 AWG	--
5	QPI4M25X03D	100	VINYL MALE DISCONNECT	16-14 AWG	--
6	QPI4F25X03D	100	VINYL FEMALE DISCONNECT	16-14 AWG	--
7	QPI0M25X03D	100	VINYL MALE DISCONNECT	12-10 AWG	--
8	QPI0F25X03D	50	VINYL FEMALE DISCONNECT	12-10 AWG	--
9	TPI010	50	VINYL RING	12-10 AWG	#10
10	TPI610	100	VINYL RING	22-16 AWG	#10
11	TPI410	100	VINYL RING	16-14 AWG	#10
12	TPI010LF	50	VINYL LOCKING FORK	12-10 AWG	#10
13	TPI66LF	100	VINYL LOCKING FORK	22-16 AWG	#6
14	SPI0	50	VINYL SPLICE	12-10 AWG	--
15	TPI48LF	100	VINYL LOCKING FORK	16-14 AWG	#8
16	SPI6	100	VINYL SPLICE 22-16 AWG	22-16 AWG	--
17	SPI4	100	VINYL SPLICE 16-14 AWG	16-14 AWG	--

REV.	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	04/25/2017 00:00:00 AM	FOCUS REQUEST FPN1704075	46578	CV	MB

VIEW OF INSIDE COVER WHEN OPENED



REV: PE0200

TO ORDER BURNDY® PRODUCTS CALL		STKIT1602MRE1022NV COMPRESSION SYSTEM	
UNITED STATES: 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: 50081930	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: STKIT1602MRE1022NV	
FOR PRODUCT INFO: <a href="http://www.burndy.com">http://www.burndy.com</a>		DRAWN BY: C.VIMAL 04/25/2017	
		CHECKER: B.MANIKANDAN 04/25/2017	
		DSN APPVL: --	
		MFG APPVL: --	
		QA APPVL: --	
		MKT APPVL: --	
		PROD FAM: --	
		PROJECT #: FPN1704075	
		DOCUMENT TYPE: Sales	
		REL LEVEL: Released	
		SCALE: 1:8	
		DRAWING NO	
		50081302	
		REV	
		A	
		SHEET 1 OF 1	

