



NOTE:

1. TO OBTAIN FITTINGS WITH GALV. STEEL HWD. CHANGE LAST TWO DIGITS OF CAT. NO. TO G1, G2, ETC. EXAMPLE-GC-141-G1 = GC-141-01 WITH GALV. HDWE.
2. BOLT LENGTH PROVIDED FOR CONNECTING TO A .250" BAR, WHEN LONGER BOLTS ARE REQUIRED ADD PLATE THICKNESS AFTER CAT. NO. EXAMPLE - GC-141-01-1/2 = BOLT LENGTH FOR .500" PLATE.
3. FOR ALUM. CONN. ADD PREFIX 'A' TO CAT NO. EXP.-AGC-141-G1. ASSEMBLY WILL BE FURNISHED WITH GALV. STEEL HARDWARE.
4. CABLE RANGE FOR AGC-141-G1 IS #4STR TO 2/0 STR ALUM. CABLE.
5. ITEMS WITH "WOR" SUFFIX HAVE WRENCH CLEARANCE AROUND BOLT HEAD. EXAMPLE: GC-141A-02-WOR
6. FOR PARTS TO BE SUPPLIED WITH BELLEVILLE WASHER ADD "BW" SUFFIX TO CAT. NO. (EXAMPLE: GC141A02BW)
7. GC14101AP HAS WRENCH CLEARANCE AROUND BOLT HEAD.
8. ITEMS WITH "ED" SUFFIX ARE SUPPLIED WITH SILICON BRONZE HARDWARE.
9. ADD "TP" SUFFIX FOR TIN PLATED CASTINGS

MATERIAL :
 BODY-CAST BRONZE
 HARDWARE-STAINLESS STEEL

CATALOG NUMBER	CABLE RANGE		DIMENSION IN INCHES						
	MIN.	MAX.	A	B	C	J	K	L	H
GC-141-01	#6 SOL	2/0 STR.	1.250	1.563	2.000	.500	.250		
GC-141-01-AP	#6 SOL	2/0 STR.	1.625	1.563	2.000	.500	.250		
GC-141A-02	#4 SOL	300 MCM	1.500	1.938	2.125	.500	.250		1.281
GC-141-03	300 MCM	500 MCM	2.000	2.500	2.375	.500	.250		
GC-141-04	500 MCM	800 MCM	1.875	2.750	2.750	.500	.250		
GC-141-05	800 MCM	1000 MCM	2.000	2.875	3.000	.500	.250		
GC-141-06	#4 SOL	2/0 STR.	1.688	1.688	2.125	.625	.250		
GC-141-07	#4 SOL	300 MCM	1.688	2.063	2.250	.625	.250		
GC-141-08	300 MCM	500 MCM	2.188	2.563	2.500	.625	.250		
GC-141-09	500 MCM	800 MCM	2.188	2.813	2.625	.625	.250		
GC-141-10	800 MCM	1000 MCM	2.188	2.938	3.375	.625	.250		
GC-141-00	#8 SOL	#4 STR.	1.375	1.375	2.000	.375	.250		
GC-141-11	1000MCM	1250 MCM	2.500	3.250	3.875	.625	.250		
GCB-141-01	#4 SOL	2/0 STR.	1.500	1.625	2.000	.500	.250	.656	
GCB-141-02	#4 SOL	300 MCM	1.500	2.000	2.125	.500	.250	.656	
GC-141-3-01	#6 SOL	2/0 STR.	1.625	2.000	1.750	.375	.250		

76889	1/4/2019	HG	HG	ANDERSON	HUBBELL® POWER SYSTEMS
EC #	DATE	CHG BY	RESP ENG		
DESC OF DWG: CHANGE LOOK OF BOLT AND WASHER IN MODEL ADD GC14101AP				TITLE GROUND CLAMP TYPES GC-141 & GCB-141	
REASON (S) FOR CHANGE: ADD NOTE 6				CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.	SIZE C
DISPOSITION OF MAT'L: --				DWG NO. C-2564	CAT / PART / ASSY NO. SEE TABLE
				DO NOT SCALE THIS DRAWING	DRN BY CW
				DATE 3-16-56	SHEET 1 OF 1