




REV	DATE	DESCRIPTION	EC	BY	C'HK.
E	03/09/2021	NOTES & TABLE UPDATION	210308005677	SS	KC

JACKETED CONCENTRIC NEUTRAL 15 kV					
BURNDY SLEEVE CATALOG NUMBER 	BURNDY SLEEVE ITEM NUMBER	SLEEVE RANGE	INSULATION DIAMETER RANGE	INSULATION DIAMETER (PRESHRINK)	STANDARD PACKAGE QUANTITY
CSUDO15210J	50104438	#2 - 1/0	0.57-0.90 [14.5-23]	1.10 [28]	1

JACKETED CONCENTRIC NEUTRAL 25/28 Kv					
BURNDY SLEEVE CATALOG NUMBER 	BURNDY SLEEVE ITEM NUMBER	SLEEVE RANGE	INSULATION DIAMETER RANGE	INSULATION DIAMETER (PRESHRINK)	STANDARD PACKAGE QUANTITY
CSUDO2528140J	50104443	#1 - 4/0	0.71-1.26 [18-32]	1.50 [38]	1
CSUDO252810250J	50104444	1/0 - 250	0.83-1.34 [21-34]	1.65 [42]	

NOTES:

- MATERIAL: SILICONE RUBBER
-  INCLUDES: (COLD SHRINK TERMINATION SUB ASSEMBLY, ENDSEAL TERMINATION, CTSR ENDSEAL TERMINATION, INSTALLATION GUIDE, CUTBACK TEMPLATE).
- DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED AND ARE FOR REFERENCE ONLY.
- CONFORMS TO IEEE-48-2009, CLASS 1 STANDARDS.
- CONFORMS TO ISO/IEC 17025 STANDARDS.
- RUS APPROVED.
- REPORT # K-423192-RC-0000-R00.



TO ORDER BURNDY® PRODUCTS CALL		35 KV COLD SHRINK G SERIES SLEEVE													
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: SEE TABLE													
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: SEE TABLE													
FOR PRODUCT INFO: http://www.burndy.com		<table border="1"> <tr> <td>DRAWN BY: R. BABU</td> <td>12/13/2018</td> </tr> <tr> <td>CHECKER: K. JAYAVIGNESH</td> <td>9/3/2019</td> </tr> <tr> <td>DSN APRVL: K. CASTONGUAY</td> <td>10/17/2019</td> </tr> <tr> <td>MFG APRVL:</td> <td></td> </tr> <tr> <td>QA APRVL: B. ELLIOTT</td> <td>10/17/2019</td> </tr> <tr> <td>MKT APRVL: K. BOUTIN</td> <td>10/17/2019</td> </tr> </table>		DRAWN BY: R. BABU	12/13/2018	CHECKER: K. JAYAVIGNESH	9/3/2019	DSN APRVL: K. CASTONGUAY	10/17/2019	MFG APRVL:		QA APRVL: B. ELLIOTT	10/17/2019	MKT APRVL: K. BOUTIN	10/17/2019
DRAWN BY: R. BABU	12/13/2018														
CHECKER: K. JAYAVIGNESH	9/3/2019														
DSN APRVL: K. CASTONGUAY	10/17/2019														
MFG APRVL:															
QA APRVL: B. ELLIOTT	10/17/2019														
MKT APRVL: K. BOUTIN	10/17/2019														
PROJ FAM:		DRAWING NO	REV												
PROJECT #:		50095766	E												
DOCUMENT TYPE: Sales		SIZE													
REL LEVEL: Released		B													
		SHEET 1 OF 4													

REV	DATE	DESCRIPTION	EC	BY	C'H.K.
E	03/09/2021	NOTES & TABLE UPDATION	210308005677	SS	KC

BARE CONCENTRIC NEUTRAL 15 KV					
BURNDY SLEEVE CATALOG NUMBER	BURNDY SLEEVE ITEM NUMBER	SLEEVE RANGE	INSULATION DIAMETER RANGE	INSULATION DIAMETER (PRESHRINK)	STANDARD PACKAGE QUANTITY
CSUDO15210B	50104447	#2 - 1/0	0.57-0.90 [14.5-23]	1.10 [28]	1

BARE CONCENTRIC NEUTRAL 25/28 KV					
BURNDY SLEEVE CATALOG NUMBER	BURNDY SLEEVE ITEM NUMBER	SLEEVE RANGE	INSULATION DIAMETER RANGE	INSULATION DIAMETER (PRESHRINK)	STANDARD PACKAGE QUANTITY
CSUDO2528140B	50104452	#1 - 4/0	0.71-1.26 [18-32]	1.50 [38]	1
CSUDO252810250B	50104453	1/0 - 250	0.83-1.34 [21-34]	1.65 [42]	

NOTES:

1. MATERIAL: SILICONE RUBBER
2. INCLUDES: (COLD SHRINK TERMINATION SUB ASSEMBLY,CTSR ENDSEAL TERMINATION, INSTALLATION GUIDE).
3. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED AND ARE FOR REFERENCE ONLY.
4. CONFORMS TO IEEE-48-2009, CLASS 1 STANDARDS.
5. CONFORMS TO ISO/IEC 17025 STANDARDS.
6. RUS APPROVED.
7. REPORT # K-423192-RC-0000-R00.



TO ORDER BURNDY® PRODUCTS CALL		35 KV COLD SHRINK G SERIES SLEEVE												
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: SEE TABLE												
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO:SEE TABLE												
FOR PRODUCT INFO: http://www.burndy.com		<table border="1"> <tr> <td>DRAWN BY: R.BABU</td> <td>12/13/2018</td> <td rowspan="5"> </td> </tr> <tr> <td>CHECKER: K.JAYAVIGNESH</td> <td>9/3/2019</td> </tr> <tr> <td>DSN APRVL: K.CASTONGUAY</td> <td>10/17/2019</td> </tr> <tr> <td>MFG APRVL: B.ELLIOTT</td> <td>10/17/2019</td> </tr> <tr> <td>MKT APRVL: K.BOUTIN</td> <td>10/17/2019</td> </tr> </table>		DRAWN BY: R.BABU	12/13/2018		CHECKER: K.JAYAVIGNESH	9/3/2019	DSN APRVL: K.CASTONGUAY	10/17/2019	MFG APRVL: B.ELLIOTT	10/17/2019	MKT APRVL: K.BOUTIN	10/17/2019
DRAWN BY: R.BABU	12/13/2018													
CHECKER: K.JAYAVIGNESH	9/3/2019													
DSN APRVL: K.CASTONGUAY	10/17/2019													
MFG APRVL: B.ELLIOTT	10/17/2019													
MKT APRVL: K.BOUTIN	10/17/2019													
PROJ #:	SIZE	DRAWING NO	REV											
PROJECT #:	B	50095766	E											
DOCUMENT TYPE: Sales		SHEET 2 OF 4												
REL LEVEL: Released														

JACKETED CONCENTRIC NEUTRAL 35 kV					
BURNDY SLEEVE CATALOG NUMBER	BURNDY SLEEVE ITEM NUMBER	SLEEVE RANGE	INSULATION DIAMETER RANGE	INSULATION DIAMETER (PRESHRINK)	STANDARD PACKAGE QUANTITY
CSUDO3510350J	50100526	1/0 - 350	1.04 - 1.63 [34.03 - 58.92]	1.97 [71.88]	1
CSUDO355001500J	50100527	350 - 1500	1.34 - 2.32 [34.03 - 58.92]	2.83 [71.88]	

SHEILDED CONCENTRIC NEUTRAL 35 kV					
BURNDY SLEEVE CATALOG NUMBER	BURNDY SLEEVE ITEM NUMBER	SLEEVE RANGE	INSULATION DIAMETER RANGE	INSULATION DIAMETER (PRESHRINK)	STANDARD PACKAGE QUANTITY
CSGO3550015	50105005	1/0 - 350	1.04 - 1.63 [34.03 - 58.92]	1.97 [50.03]	3
CSGO355001500	50105035	350 - 1500	1.34 - 2.32 [37.03 - 58.92]	2.83 [71.88]	

NOTES:

- MATERIAL: SILICONE RUBBER
- INCLUDES: (COLD SHRINK TERMINATION SUB ASSEMBLY,CTSR ENDSEAL TERMINATION, INSTALLATION GUIDE).
- DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED AND ARE FOR REFERENCE ONLY.
- CONFORMS TO IEEE-48-2009, CLASS 1 STANDARDS.
- CONFORMS TO ISO/IEC 17025 STANDARDS.
- RUS APPROVED.
- REPORT # K-423192-RC-0000-R00.

REV	DATE	DESCRIPTION	EC	BY	C'H'K.
E	03/09/2021	NOTES & TABLE UPDATION	210308005677	SS	KC



TO ORDER BURNDY® PRODUCTS CALL		35 kV COLD SHRINK G SERIES SLEEVE															
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: SEE TABLE															
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: SEE TABLE															
FOR PRODUCT INFO: http://www.burndy.com		<table border="1"> <tr> <td>DRAWN BY: R. BABU</td> <td>12/13/2018</td> <td rowspan="5"> </td> </tr> <tr> <td>CHECKER: K. JAYAVIGNESH</td> <td>9/3/2019</td> </tr> <tr> <td>DSN APRVL: K. CASTONGUAY</td> <td>10/17/2019</td> </tr> <tr> <td>MFG APRVL:</td> <td></td> </tr> <tr> <td>QA APRVL: B. ELLIOTT</td> <td>10/17/2019</td> </tr> <tr> <td>MKT APRVL: K. BOUTIN</td> <td>10/17/2019</td> <td></td> </tr> </table>		DRAWN BY: R. BABU	12/13/2018		CHECKER: K. JAYAVIGNESH	9/3/2019	DSN APRVL: K. CASTONGUAY	10/17/2019	MFG APRVL:		QA APRVL: B. ELLIOTT	10/17/2019	MKT APRVL: K. BOUTIN	10/17/2019	
DRAWN BY: R. BABU	12/13/2018																
CHECKER: K. JAYAVIGNESH	9/3/2019																
DSN APRVL: K. CASTONGUAY	10/17/2019																
MFG APRVL:																	
QA APRVL: B. ELLIOTT	10/17/2019																
MKT APRVL: K. BOUTIN	10/17/2019																
PROJ #:	SIZE	DRAWING NO	REV														
50095766	B	50095766	E														
DOCUMENT TYPE: Sales		SHEET 3 OF 4															
REL LEVEL: Released																	

REV	DATE	DESCRIPTION	EC	BY	C'H'K.
E	03/09/2021	NOTES & TABLE UPDATION	210308005677	SS	KC

G-SERIES-OUTDOOR					
BURNDY SLEEVE CATALOG NUMBER	BURNDY SLEEVE ITEM NUMBER	SLEEVE RANGE	INSULATION DIAMETER RANGE	INSULATION DIAMETER (PRESHRINK)	STANDARD PACKAGE QUANTITY
CSGO3550015	50105005	1/0 - 350	1.04 - 1.63 [34.03 - 58.92]	1.97 [50.03]	3
CSGO355001500	50092013	350 -1500	1.34 - 2.32 [37.03 - 58.92]	2.83 [71.88]	



NOTES:

1. MATERIAL: SILICONE RUBBER
2. INCLUDES: (COLD SHRINK TERMINATION SUB ASSEMBLY,CTSR ENDSEAL TERMINATION, INSTALLATION GUIDE).
3. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED AND ARE FOR REFERENCE ONLY.
4. CONFORMS TO IEEE-48-2009, CLASS 1 STANDARDS.
5. CONFORMS TO ISO/IEC 17025 STANDARDS.
6. RUS APPROVED.
7. REPORT # K-423192-RC-0000-R00.

TO ORDER BURNDY® PRODUCTS CALL		35 KV COLD SHRINK G SERIES SLEEVE															
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: SEE TABLE															
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO:SEE TABLE															
FOR PRODUCT INFO: http://www.burndy.com		<table border="1"> <tr> <td>DRAWN BY: R.BABU</td> <td>12/13/2018</td> <td rowspan="5"> </td> </tr> <tr> <td>CHECKER: K.JAYAVIGNESH</td> <td>9/3/2019</td> </tr> <tr> <td>DSN APRVL: K.CASTONGUAY</td> <td>10/17/2019</td> </tr> <tr> <td>MFG APRVL:</td> <td></td> </tr> <tr> <td>QA APRVL: B.ELLIOTT</td> <td>10/17/2019</td> </tr> <tr> <td>MKT APRVL: K.BOUTIN</td> <td>10/17/2019</td> <td></td> </tr> </table>		DRAWN BY: R.BABU	12/13/2018		CHECKER: K.JAYAVIGNESH	9/3/2019	DSN APRVL: K.CASTONGUAY	10/17/2019	MFG APRVL:		QA APRVL: B.ELLIOTT	10/17/2019	MKT APRVL: K.BOUTIN	10/17/2019	
DRAWN BY: R.BABU	12/13/2018																
CHECKER: K.JAYAVIGNESH	9/3/2019																
DSN APRVL: K.CASTONGUAY	10/17/2019																
MFG APRVL:																	
QA APRVL: B.ELLIOTT	10/17/2019																
MKT APRVL: K.BOUTIN	10/17/2019																
PROJ FAM:	DRAWING NO	REV															
PROJECT #:	SIZE	50095766	E														
DOCUMENT TYPE: Sales	B	SHEET 4 OF 4															
REL LEVEL: Released																	