

PATRIOT®

BATTERY ACTUATED TOOL - HYDRAULIC SELF CONTAINED - 11 TON OUTPUT FORCE - T3 TECHNOLOGY

SPECIFICATIONS

- CRIMP FORCE: 11 TONS (10.0 METRIC TONS)
- TOOL WEIGHT: 16.5 LBS (7.5 kg)
- LENGTH: 16.9 (42.9 cm)
- WIDTH: 3.25 (8.26 cm)
- HEIGHT: 14.95 (37.97 cm)
- OPERATING VOLTAGE: 18V-DC
- RECHARGE TIME: 30 MINUTES

FEATURES AND BENEFITS

- REFINED HYDRAULIC SYSTEM FOR SUPERIOR PERFORMANCE, SPEED AND RELIABILITY.
- FIELD PROVEN ELECTRONICS FOR ULTIMATE RELIABILITY IN THE HARSHTEST ENVIRONMENTS.
- OVERMOLDED HANDLE FOR COMFORT AND IMPROVED GRIP; ALLOWS FOR ONE-HANDED OPERATION FOR ADVANCE, RETRACT AND HOLD.
- 18 VOLT LITHIUM-ION BATTERIES PROVIDE 2.5 TIMES MORE CHARGE / DISCHARGE CYCLES THAN TRADITIONAL Ni-Cd BATTERIES AND PROVIDE 430% MORE LIFETIME WORK.
- 30 MINUTE CHARGER CONTROLS CURRENT, VOLTAGE AND TEMPERATURE TO MAXIMIZE BATTERY LIFE. FORCED AIR COOLING FAN COOLS THE BATTERY BY FORCING COOL AIR THROUGH THE BATTERY'S BUILT-IN AIR VENTS.
- STATE OF THE ART "C" SHAPED CRIMPING HEAD DESIGN, 355° ROTATION LETS THE USER GET INTO TIGHT AREAS EASIER.
- DIELESS SYSTEM ELIMINATES THE NEED TO PURCHASE AND MAINTAIN DIES.
- DIELESS SYSTEM ALLOWS CONNECTORS AND SPLICES TO BECOME RANGE TAKING.
- ERGONOMICALLY BALANCED TOOL DESIGN EASES OPERATION AND HELPS LESSEN FATIGUE.
- DURABLE HIGH IMPACT FORMED CARRYING CASE PROVIDES SUPERIOR PROTECTION AND STORES ALL ACCESSORIES.
- 5 YEAR LIMITED WARRANTY ON THE TOOL, 3 YEAR LIMITED WARRANTY ON THE BATTERIES AND CHARGER.
- LIFETIME WARRANTY ON THE INFINITY® DRIVE.

T3 TECHNOLOGY FEATURES AND BENEFITS

TRACK

- ON-BOARD GPS CHIP TRACKS LATITUDE AND LONGITUDE.
- CAPTURES & MAPS CRIMP LOCATIONS WITH BURNDY T3 APP.
- RECORDS DATE AND TIME EVERY CRIMP WAS MADE.
- MONITOR JOB PROGRESS OR LOCATE POTENTIAL ISSUE CRIMPS.

TRACE

- RED/GREEN VERIFICATION LIGHT VALIDATES OUTPUT FORCE.
- ADD CUSTOM COMMENT TO ANY AND ALL CRIMPS IN APP.
- MANAGE AND SHARE T3 TOOLS WITH SECURE ACCOUNTS.
- GENERATE & CUSTOMIZE REPORTS TO SHARE WITH INSPECTORS.


TRANSMIT

- BLUETOOTH® TECHNOLOGY CONNECTS TO PHONES AND TABLETS.
- DATA SENT TO CLOUD WITH AES 256-BIT ENCRYPTION.
- REMOTELY TRIGGER WORK LIGHT TO FIND TOOL IN THE DARK.
- FIRMWARE UPDATES AVAILABLE AS THEY ARE RELEASED.

NOTES:

1. LANYARD IS STORED IN COMPARTMENT UNDER THE LID.

2. TOOL ACCEPTS 18V MAKITA LITHIUM ION BATTERIES, BL SERIES OF SIZE 2.0 AHR AND GREATER. THE "STAR" MOLDED INTO THE BATTERY CLIP IDENTIFIES ACCEPTANCE OF THE BL SERIES BATTERIES.



TO ORDER BURNDY® PRODUCTS CALL

UNITED STATES:
1-800-346-4175 (LONDONDERRY, NH)

CANADA:
1-800-361-6975 (QUEBEC)
1-800-387-6487 (ALL OTHER PROVINCES)

FOR PRODUCT INFO: <http://www.burndy.com>

PAT444ST3 KIT ASSEMBLY

ITEM NO: --	SCALE: 7:32
CAT. NO: SEE TABLE SHEET 2	DRAWING NO
DRAWN BY: T. FAUCHER 02/03/2020	REV
CHECKER: B. WHITE 02/04/2020	50108199
DSN APPVL: B. WHITE 04/03/2020	SHEET 1 OF 2
MFG APPVL: S. BURNS 04/08/2020	A
QA APPVL: G. REDFIELD 04/06/2020	
MKT APPVL: M. GUARRERA 04/06/2020	
PROD FAM: TOOLS, BATTERY	
PROJECT #: NPD-03142	
DOCUMENT TYPE: Sales	
REL LEVEL: Released	

REV.	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	2020-04-08 00:00:00 EDT	DRAWING RELEASED	52924	TRF	BW

REV.	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	2020-04-08 00:00:00 EDT	DRAWING RELEASED	52924	TRF	BW

EXAMPLE CATALOG NUMBER: PAT444ST3U03A2

FIXED VALUE
 PAT444ST3 U

03

A

2

HEAD TYPE					BATTERY					CHARGER					CASE				
CODE	ITEM NUMBER	CATALOG NO.	QTY	DESCRIPTION	CODE	ITEM NUMBER	CATALOG NO.	QTY	DESCRIPTION	CODE	ITEM NUMBER	CATALOG NO.	QTY	DESCRIPTION	CODE	ITEM NUMBER	CATALOG NO.	QTY	DESCRIPTION
U	50108195	PAT444ST3TB	1	UNCOVERED HEAD	00	--	--	0	NONE	0	--	--	0	NONE	0	--	--	0	NONE
					03	30001565	BAT18VLI	2	3 AH MAKITA LI	A	30001520	PATCHGRLI	1	AC	2	30003605	PATCASELI	1	HARD
					05	50056611	BAT18V5AHLI	2	5 AH MAKITA LI	D	30001522	PATCHGRLIDC	1	DC	3	50099346	PATPROBAG	1	NYLON

*** BILL OF MATERIAL ***

PT NO.	CATALOG NO.	QTY	DESCRIPTION
1	PAT444ST3TB	1	PAT444S WITH T3 TECH TOOL BODY - UNCOVERED HEAD
2	PATCASELI	1	CASE, TOOL PATRIOT LITHIUM ION
3	PATCHGRLI	1	CHARGER, BATTERY LITHIUM ION
4	PT208620	1	LANYARD
5	BAT18VLI	2	BATTERY, MAKITA LITHIUM ION 18V 3.0 Ah
6	PAT444ST3SOMI	1	SOMI, PAT444ST3
7	PT20443801	1	WARRANTY CARD
8	PT3QUICKSTART	1	QUICKSTART GUIDE, T3
9	PT3REGWARNING	1	REGISTRATION WARNING T3
10	LISDS	1	SDS, LITHIUM ION BATTERY

REV: PE0200

TO ORDER BURNDY® PRODUCTS CALL		PAT444ST3 KIT ASSEMBLY																															
UNITED STATES: 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: --																															
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: SEE TABLE																															
FOR PRODUCT INFO: http://www.burndy.com		<table border="1"> <tr> <td>DRAWN BY: T. FAUCHER</td> <td>02/03/2020</td> <td rowspan="6">BURNDY</td> <td rowspan="6">SCALE: 7:32</td> </tr> <tr> <td>CHECKER: B. WHITE</td> <td>02/04/2020</td> </tr> <tr> <td>DSN APPVL: B. WHITE</td> <td>04/03/2020</td> </tr> <tr> <td>MFG APPVL: S. BURNS</td> <td>04/08/2020</td> </tr> <tr> <td>QA APPVL: G. REDFIELD</td> <td>04/06/2020</td> </tr> <tr> <td>MKT APPVL: M. GUARRERA</td> <td>04/06/2020</td> </tr> <tr> <td>PROJ #:</td> <td>SIZE</td> <td>DRAWING NO</td> <td>REV</td> </tr> <tr> <td>NPD-03142</td> <td>B</td> <td>50108199</td> <td>A</td> </tr> <tr> <td>DOCUMENT TYPE: Sales</td> <td></td> <td colspan="2">SHEET 2 OF 2</td> </tr> <tr> <td>REL LEVEL: Released</td> <td></td> <td colspan="2"></td> </tr> </table>		DRAWN BY: T. FAUCHER	02/03/2020	BURNDY	SCALE: 7:32	CHECKER: B. WHITE	02/04/2020	DSN APPVL: B. WHITE	04/03/2020	MFG APPVL: S. BURNS	04/08/2020	QA APPVL: G. REDFIELD	04/06/2020	MKT APPVL: M. GUARRERA	04/06/2020	PROJ #:	SIZE	DRAWING NO	REV	NPD-03142	B	50108199	A	DOCUMENT TYPE: Sales		SHEET 2 OF 2		REL LEVEL: Released			
DRAWN BY: T. FAUCHER	02/03/2020	BURNDY	SCALE: 7:32																														
CHECKER: B. WHITE	02/04/2020																																
DSN APPVL: B. WHITE	04/03/2020																																
MFG APPVL: S. BURNS	04/08/2020																																
QA APPVL: G. REDFIELD	04/06/2020																																
MKT APPVL: M. GUARRERA	04/06/2020																																
PROJ #:	SIZE	DRAWING NO	REV																														
NPD-03142	B	50108199	A																														
DOCUMENT TYPE: Sales		SHEET 2 OF 2																															
REL LEVEL: Released																																	