




ITEM NO.	DESCRIPTION	NSOTVM6 QTY	NSOTVDM6 QTY	NSODK6 QTY
1	BASE	1	1	0
2	VOICE MODULE PCB ASSY	1	1	0
3	VOICE MODULE COVER	1	1	0
4	DATA MODULE PCB ASSY	0	1	1
5	DATA MODULE COVER	0	1	1
6	VIDEO SPLITTER	1	1	0

CATALOG NUMBER	DESCRIPTION
NSOTVM6	VOICE AND VIDEO COMBO MODULE
NSOTVDM6	VOICE AND VIDEO COMBO MODULE WITH DATA MODULE OPTION
NSODK6	DATA MODULE KIT



- NOTES:
- MATERIAL:
 - COMBO MODULE BASE: BLACK ABS
 - VOICE MODULE PCB: FR-4
 - VOICE MODULE COVER: BLACK ABS
 - DATA MODULE PCB: FR-4
 - DATA MODULE COVER: BLACK ABS
 - VIDEO SPLITTER: POTTED METALLIC BODY
 - ELECTRICAL SPECIFICATIONS:
 - VOICE MODULE: FCC PART 68 COMPLIANT
 - DATA MODULE: CAT 5e+ TIA T568A WIRED
 - VIDEO SPLITTER: OPERATING FREQUENCY RANGE 5-1000MHz
INSERTION LOSS 10dB
 - LISTED UNDER UL-1863.
 - SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE.

Created on AUTOCAD	DIMENSIONING AND TOLERANCE PER ANSI Y14.5M-1982 UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES (MM). TOLERANCES .XX = ±.01 (.25) .XXX = ±.005 (.127) .XXXX = ±.0025 (.0635) ANGLE TOL ±1°		PROJECT REFERENCE: 2007-017		 Hubbell Premise Wiring HUBBELL INCORPORATED (Delaware) 14 Lord's Hill Road, Stonington, Connecticut 06378
	IN ACCEPTING OUR DRAWINGS, BLUEPRINTS, OR SUPPORTING DOCUMENTATION FOR QUOTATION OR OTHER PURPOSES, YOU AGREE NOT TO DISCLOSE TO OTHERS THE IDEAS, INFORMATION, OR DESIGNS SHOWN HEREIN, AND THAT YOU WILL MAKE NO USE OF SAME WITHOUT PERMISSION		MATERIAL: SEE NOTES		
		DRAWN BY: B MARTINO 11/27/07		TITLE: netSELECT COMBINATION MODULE KITS	
		CHECKED BY:		SIZE: DRAWING NO. C HWS12592C	
		APPROVED BY:		REV. A	
		SCALE: NTS		SHEET 1 OF 1	

A	6187	11/27/07	INITIAL RELEASE	BTM	
REV.	ECN	DATE	DESCRIPTION	CHG BY	APPD BY