

CATALOG NO.	DESCRIPTION
OFCLICK600MPO	FIBER,CLEANCLICKER,600CLK,MPO-M/F



Product Features:
<ul style="list-style-type: none"> Click to Clean push engagement Easy view Pay Off spool for monitoring remaining cleaning capacity 13mm (0.5") material per Click, > 4 times the ferrule height

Removable Contamination List
<ul style="list-style-type: none"> ISO 12103 aka AZ road dust Skin flakes & oil residue 99% IPA residue T Shirt lint French fry grease residue Hand lotion residue Tap water residue Saw dust Drywall dust Coastal salt fog residue

Product Overview:	
Connector Systems:	<ul style="list-style-type: none"> Male MPO connectors in adapters (flat and 8° angled) Female MPO unmated MPO connectors (flat and 8° angled) MTP style connectors Other MT based connector systems*
Typical Applications:	<ul style="list-style-type: none"> MPO Cassette Modules MPO Trunk Assemblies QSFP+ Modules CFP Modules

NOTES:

- KIT SHOULD CONTAIN:
 - (1) CLEAN CLICKER CONNECTOR CLEANER IN A BOX (8.50 X 2.125 X .75)
- SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE.

1	21320	09/22/15	INITIAL RELEASE	MMA	
REV.	ECN	DATE	DESCRIPTION	CHG BY	APPD BY

Created on INVENTOR

DIMENSIONING AND TOLERANCE PER ANSI Y14.5M-1982 UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES (MM). TOLERANCES.XX = ±.01 (.25)
 .XXX = ±.005 (.127)
 .XXXX = ±.0025 (.0635)
 ANGLE TOL ±1°

IN ACCEPTING OUR DRAWINGS, BLUEPRINTS, OR SUPPORTING DOCUMENTATION FOR QUOTATION OR OTHER PURPOSES, YOU AGREE NOT TO DISCLOSE TO OTHERS THE IDEAS, INFORMATION, OR DESIGNS SHOWN HEREIN, AND THAT YOU WILL MAKE NO USE OF SAME WITHOUT PERMISSION

PROJECT REFERENCE: NPD-00162
MATERIAL: SEE NOTES
DRAWN BY: MABBY 08/18/15
CHECKED BY:
APPROVED BY:

		Hubbell Premise Wiring HUBBELL INCORPORATED (Delaware) 23 CLARA DRIVE, SUITE 103 MYSTIC, CT 06355	
TITLE: MPO FIBER OPTIC CONNECTOR CLEANER			
SIZE C	DRAWING NO. HWS14539C	REV. 1	
SCALE: N/A		SHEET 1 OF 1	