






CATALOG NUMBER	DESCRIPTION	ADAPTER COLOR
FSPNLCDS3AQ	FIBER, ADAPT PNL,6P,3LC,DUPLX,ZIRC,AQ	AQUA
FSPNLCDS3B	FIBER, ADAPT PNL,6P,3LC DUPLX,ZIRC,BL	BLUE
FSPNLCDS3BE	FIBER, ADAPT PNL,6P,3LC DUPLX,ZIRC,BE	BEIGE
FSPNLCDS3BK	FIBER, ADAPT PNL,6P,3LC DUPLX,ZIRC,BK	BLACK
FSPNLCDS3GN	FIBER, ADAPT PNL,6P,3LC DUPLX,ZIRC,GN	GREEN
FSPNLCDS3OR	FIBER, ADAPT PNL,6P,3LC DUPLX,ZIRC,OR	ORANGE
FSPNLCDS3R	FIBER, ADAPT PNL,6P,3LC DUPLX,ZIRC,RD	RED
FSPNLCDS3VI	FBR,ADAPT PNL,6P,3LC DUPLX,ZIRC,EVI	ERIKA VIOLET
FSPNLCDS3Y	FIBER, ADAPT PNL,6P,3LC DUPLX,ZIRC,YL	YELLOW



NOTES:

- PANEL MATERIAL: COLD ROLLED STEEL, BLACK POWDER COAT
- SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE.

REV.	ECN	DATE	DESCRIPTION	CHG BY	APPD BY
1	210121004122	1/21/21	INITIAL RELEASE	DPO	MMA

Created on INVENTOR	DIMENSIONING AND TOLERANCE PER ANSI Y14.5M-1982 UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES (MM). TOLERANCES:XX = ±.01 (.25) .XXX = ±.005 (.127) .XXXX = ±.0025 (.0635) ANGLE TOL ±1°		PROJECT REFERENCE: NPD-03368		 Hubbell Premise Wiring HUBBELL INCORPORATED (Delaware) 23 CLARA DRIVE, SUITE 103 MYSTIC, CT 06355	
	IN ACCEPTING OUR DRAWINGS, BLUEPRINTS, OR SUPPORTING DOCUMENTATION FOR QUOTATION OR OTHER PURPOSES, YOU AGREE NOT TO DISCLOSE TO OTHERS THE IDEAS, INFORMATION, OR DESIGNS SHOWN HEREIN, AND THAT YOU WILL MAKE NO USE OF SAME WITHOUT PERMISSION		MATERIAL: SEE NOTES			
			DRAWN BY: D. O'CONNOR 1/21/21		TITLE: SIX PACK PANEL WITH 3 LC DUPLEX ADAPTERS	
			CHECKED BY: APPROVED BY: 		SIZE: C DRAWING NO.: HWS14968C REV.: 1 SCALE: N/A SHEET 1 OF 1	