


LEAD SECTION



HELIX EXTENSION




EXTENSION

LEAD SECTION						
CATALOG NUMBER	"A"	"B"	"C"	"D"	"E"	FINISH
C1101256	10	12	--	--	60	GALV
C1100569	6	8	10	--	60	GALV
C1100570	8	10	12	--	60	GALV
C1100571	6	8	10	12	79	GALV
C1100572	14	14	14	--	122	GALV
C1100573	8	10	12	14	122	GALV
C1100791	10	12	14	--	79	GALV
C1100791NG	10	12	14	--	79	BLACK

HELIX EXTENSION					
CATALOG NUMBER	"A" DIM	"B" DIM	"C" DIM	"D" DIM	FINISH
C1100577	14	--	--	42	GALV.
C1140220	14	--	--	42	BLACK
C1101304	12	--	--	42	GALV.
C1100581	14	14	--	79	GALV.
C1100586	14	14	14	122	GALV.

EXTENSION		
CATALOG NUMBER	"L"	FINISH
C1100563	37	GALV
C1100564	58	GALV
C1140210	58	BLACK
C1100565	80	GALV
C1100566	123	GALV



CHAIN SHACKLE
C110-0537 (GALV)

-NOTES-

1. ITEMS MARKED "GALV" ARE HOT DIP GALVANIZED PER ASTM A153-(LATEST REV.)
2. COUPLING BOLTS: 1-1/8" DIAMETER X 4-1/4" LONG HEX HEAD PER ASTM A193 GRADE B7.
3. ALLOWABLE TORQUE CAPACITY - 16,000 FT-LBS.
4. ULTIMATE CAPACITY FOR AXIALLY LOADED FOUNDATION (TENSION/COMPRESSION LOADS) - 150 KIPS.
5. ALL DIMENSIONS IN INCHES.

CHANCE		HUBBELL POWER SYSTEMS	
CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED. ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.		TITLE SS200 ANCHORS	
SIZE C	DWG NO. SA11010019	REV M	
DO NOT SCALE THIS DRAWING	DRN BY TLR	DATE 4/24/19	SHEET 1/1