


PART NO	SIZE	"A"	"B"	"C"	THD	"D"	"E"	MATERIAL	BURNDY CRIMP DIE	
									BARREL	SHROUD
C6002618	#2	5.75	2.06	5/8-11UNC-2A	.776	.687	ALUMINUM	U165	U166	
C6002619	1/0	5.75	2.06	5/8-11UNC-2A	.885	.687	ALUMINUM	U165	U168	
C6002620	2/0	5.75	2.06	5/8-11UNC-2A	.908	.687	ALUMINUM	U165	U-L	
C6002621	4/0	5.75	2.00	5/8-11UNC-2A	1.023	.906	ALUMINUM	U249	U-L	
C6002622	#2	5.75	2.06	5/8-11UNC-2A	.776	.687	COPPER	U165	U166	
C6002623	1/0	5.75	2.06	5/8-11UNC-2A	.885	.687	COPPER	U165	U168	
C6002624	2/0	5.75	2.06	5/8-11UNC-2A	.908	.687	COPPER	U165	U-L	
C6002625	4/0	5.75	2.00	5/8-11UNC-2A	1.023	.813	COPPER	U166	U-L	
C6003115	#2	5.75	2.06	5/8-11UNC-2A	.776	.687	TIN PLATED COPPER	U165	U166	
C6003116	1/0	5.75	2.06	5/8-11UNC-2A	.885	.687	TIN PLATED COPPER	U165	U168	
C6003117	2/0	5.75	2.06	5/8-11UNC-2A	.908	.687	TIN PLATED COPPER	U165	U-L	
C6003118	4/0	5.75	2.00	5/8-11UNC-2A	1.023	.813	TIN PLATED COPPER	U166	U-L	

CHANCE		 HUBBELL POWER SYSTEMS <small>POWER SYSTEMS, INC.</small>	
<small>CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED. ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.</small>			
TITLE		SHROUDED, THREADED GROUNDING FERRULES	
SIZE	DWG NO.	CAT / PART / ASSY NO.	REV
B	SA600-2618	SEE CHART	B
DO NOT SCALE THIS DRAWING	DRN BY TLK	DATE 6/8/20	SHEET 01 OF 01