

REV.	DATE	DESCRIPTION	ECO	BY	C'K'D.
B	05/05/08	REVERSE C44 TUBE REDUCTION CHNG.	15655	RB	RB

CONDUCTOR			BOLT SIZE	CATALOG NO.	FIG. NO.	DIMENSIONS								INSTALLATION TOOLING (# CRIMPS)							
FLEX	CODE (AWG)	NAVY				B	C	H	K	L	N	O.D.	T REF.	Z MIN.	DIE INDEX	COLOR CODE	HYDRAULIC			DIELESS (# CRIMPS)	WIRE STRIP LENGTH
		5													Y750 Y35 Y39	Y46 4	Y45 3				
777.7 kcmil 1925/24 (750 kcmil FLEX)	--	--	1/2	YAG44L-TC12-LD	1	1.65 [42]	2.18 [55]	---		3.85 [98]		1.50 [38]	.33 [8]								
				YAG44L-TC12-LD-45	2	↑	↑		.53 [13]	3.81 [97]	.53 [13]	↑	↑	.55 [14]			U44XRT UR4141WE (2)	U44XRT UR4141WE (2)	U44XRT UR4141WE (2)		1-5/8'
				YAG44L-TC12-LD-90	3				3.11 [79]	3.35 [85]		4.10 [104]									
777.7 kcmil 1925/24 (750 kcmil/FLEX)	--	--	5/8	YAG44L-TC58-LD	1	↓	↓	---		4.06 [103]		1.50 [38]	.33 [8]								
				YAG44L-TC58-LD-45	2				.69 [17]	4.06 [103]	.66 [17]	↓	↓	.67 [17]			U44XRT UR4141WE (2)	U44XRT UR4141WE (2)	U44XRT UR4141WE (2)		1-5/8'
				YAG44L-TC58-LD-90	3				3.11 [79]	3.35 [85]		2.32 [59]									

SEE SHEET 1 OF 18 FOR NOTES

TO ORDER BURNDY® PRODUCTS CALL UNITED STATES: 1-800-346-4175 (LONDONDERRY, NH) CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES) FOR PRODUCT INFO: <a href="http://www.burndy.com">http://www.burndy.com</a>	HYLUG™	
	ITEM NO: N/A	
	CAT NO: YAG44L-TC-LD- (TABLE)	
	SCALE: 1/1	<b>BURNDY</b>
	DRAWN BY: D FILLION 12/17/92	
	CHECKER: KAY HENRY 12/18/92	
	DSN APPVL: PALAGI/HESKEY 12/22/92	
	MFG APPVL: -- --	
	QC APPVL: A LLOYD 12/31/92	DRAWING NO
	MKT APPVL: T NELSON 01/12/93	REV
PROD FAM: --	SE208132	
PROJECT #: --	B	
DOCUMENT TYPE: Sales	SIZE	
REL LEVEL: AutoCAD	D	
	SHEET 18 OF 18	