

DRAWING NO.
SC057553-01

4


3

2

1

CAT. NO.	STUD SIZE	"G" DIA.		"W" DIA.		"X" MIN.	"A" MAX.
		MAX.	MIN.	MAX.	MIN.		
YAESION11	6"	.152	.142	.380	.368	.255	1.120
YAESION56	8"	.178	.168	.380	.368	.255	1.120
YAESION12	10"	.203	.193	.380	.368	.255	1.120
YAESION57	1/4	.275	.260	.536	.524	.370	1.322
YAESION13	5/16	.338	.323	.536	.524	.370	1.322
YAESION14	3/8	.400	.385	.583	.573	.400	1.338
YAESION58	5/8	.527	.517	.727	.708	.450	1.485

REV	DATE	DESCRIPTION	ECO	BY	C' H' K.
D	02/19/2013 00:00:00 AM	UPDATE VOLTAGE RATING TO 600V FOR YAES DRAWING	30497	PM	MB



NOTES:

- 1 MATERIAL: INSULATION: NYLON (COLOR YELLOW)
TERMINAL: COPPER
- 2 FINISH: TERMINAL; TIN PLATE
- 3 "H" MAX. & MIN. DIMENSIONS SHALL BE ONE HALF OF "W" MAX. & MIN. DIMENSIONS, RESPECTIVELY.
- 4 THESE TERMINALS MEET DIMENSIONAL REQUIREMENTS OF CLASS 1, MS025036.
- 5 UL LISTED: 600 Volts, 105° C MAX.
- 6 TO ORDER SILVER PLATED LUGS ADD "SV" FOR SUFFIX.

ACCOMMODATES:
12-10 STRANDED WIRE PER MIL-W-5086

TO ORDER BURNDY® PRODUCTS CALL
 UNITED STATES:
 1-800-346-4175 (LONDONDERRY, NH)
 CANADA:
 1-800-361-6975 (QUEBEC)
 1-800-387-6487 (ALL OTHER PROVINCES)
 FOR PRODUCT INFO: <http://www.burndy.com>

INSULATED TERMINAL	
ITEM NO:	N/A
CAT. NO:	YAESION-- (SEE TABLE)
DRAWN BY:	M KOVILRAJ 11/24/09
CHECKER:	P WASON 12/18/09
DSN APPVL:	P WASON 12/18/09
MFG APPVL:	M BAILLY 03/02/10
QA APPVL:	J BRODEUR 12/22/09
MKT APPVL:	J SYLVIA 12/18/09
PROD FAM:	CM&R
PROJECT #:	--
DOCUMENT TYPE:	Sales
REL LEVEL:	Released
SCALE:	7:1
DRAWING NO	SC057553-01
REV	D
SHEET 1 OF 1	

4

3

2

1

REV: PE0200

D

D

C

C

B

B

A

A