


- ALUMINIUM ENCLOSURE IS LIGHTWEIGHT, LOW MAINTENANCE AND HAS EXCELLENT CORROSION RESISTANCE
- ALL-WELDED CONSTRUCTION: WELDS AND SEAMS ARE GROUND SMOOTH
- REMOVABLE SWINGING DOORS - DOORS HAVE STAINLESS STEEL LIFT OFF HINGES WITH STAINLESS STEEL THREE POINT LOCKING HANDLES AND RECESSED STAINLESS STEEL PENTA-HEAD BOLTS FOR SECURITY
- FINISH IS MUNSELL GREEN, OVEN CURED POWDER COAT
- ALL MOUNTING HARDWARE IS 18-8 STAINLESS STEEL
- ALUMINIUM MECHANICAL BAR CONNECTOR ELIMINATES COMPRESSION TOOLS, LUGS AND BOLT ASSEMBLIES
- UNIQUE LAY-IN FEATURE REDUCES FRUSTRATION OF FEEDING MULTIPLE CONDUCTORS THROUGH STANDARD CONNECTORS
- EACH OUTLET HAS A REMOVABLE "KEEPER" THAT ALLOWS CONDUCTORS TO BE LAID INTO THE OUTLET, SOLVING THE PROBLEM OF TRYING TO BEND LARGE CONDUCTORS IN CONFINED AREAS. THE "KEEPER" IS THEN SLID OVER THE CONDUCTOR AND THE SET-SCREWS ARE TIGHTENED. IT IS FAST AND EASY AT INITIAL INSTALLATIONS AND FOR LATER SERVICE ADDITIONS
- CONNECTORS ARE FABRICATED FROM 6061-T6 ALUMINIUM ALLOY FOR CONDUCTIVITY AND STRENGTH
- FULLY TESTED TO ANSI C119.4 FOR CLASS "A" CONNECTORS
- THREE-PHASE, NEMA 3R (RAIN-PROOF), 600 VOLT RATED, ENCLOSURE IS MADE WITH A LIFT-OFF (REMOVABLE) TOP

				TO ORDER CMC PRODUCTS		DRAWN BY: TS		NAME OF PART: ENCLOSURE ASSEMBLY		CAT. NO.: LPLE18-1000LI	
				UNITED STATES 1-513-860-4455		11-05-20		DWG NO: U22701016-S		B	
				CANADA 1-800-361-6975							
				MEXICO 011-52-722-265-4400							
				FOR PRODUCT INFO www.cmcugs.com				DRAWING NOT TO SCALE		SHEET NO: 1 OF 1	
A	NEW DRAWING CREATED		11-05-20	TS							
REV.	DESCRIPTION	ECN	DATE	INIT.							

THIS INFORMATION IS PROPRIETARY TO CONNECTOR MFG. CO. AND IS NOT TO BE DISCLOSED OUTSIDE OF CONNECTOR MFG. CO. WITHOUT A CONFIDENTIALITY AGREEMENT



CONNECTOR MANUFACTURING CO.



HAMILTON, OHIO