







M-13610

1

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
BASE	THERMOPLASTIC	BLACK
COVER	THERMOPLASTIC	COLOR PER CAT.# SEE TABLE.
BUTTON	THERMOPLASTIC	COLOR PER CAT.# SEE TABLE.

DIMENSION SHEET FOR CAT. NO.  
SEE TABLE



CPSD1xx  
SERIES

CPSD2xx  
SERIES

CPSD3xx  
SERIES

CPSD4xx  
SERIES

CPSD6xx  
SERIES

CATALOG	RAISE	LOWER	ON	OFF
CPSD1xx	-	-	-	-
CPSD2xx	1	1	1	1
CPSD3xx	1	1	-	-
CPSD4xx	1	1	2	2
CPSD6xx	*	*	*	*

\*Special order only.

SWITCH TYPE	CATALOG #	DESCRIPTION	COLOR
1 BUTTON	CPSD1W	CONTROL PANEL SWITCH, 1 BUTTON, NO PILOT, WH	WHITE
	CPSD1I	CONTROL PANEL SWITCH, 1 BUTTON, NO PILOT, IV	IVORY
	CPSD1LA	CONTROL PANEL SWITCH, 1 BUTTON, NO PILOT, LA	LIGHT ALMOND
	CPSD1GY	CONTROL PANEL SWITCH, 1 BUTTON, NO PILOT, GY	GRAY
	CPSD1BK	CONTROL PANEL SWITCH, 1 BUTTON, NO PILOT, BK	BLACK
2 BUTTONS	CPSD2W	CONTROL PANEL SWITCH, 2 BUTTON, NO PILOT, WH	WHITE
	CPSD2I	CONTROL PANEL SWITCH, 2 BUTTON, NO PILOT, IV	IVORY
	CPSD2LA	CONTROL PANEL SWITCH, 2 BUTTON, NO PILOT, LA	LIGHT ALMOND
	CPSD2GY	CONTROL PANEL SWITCH, 2 BUTTON, NO PILOT, GY	GRAY
	CPSD2BK	CONTROL PANEL SWITCH, 2 BUTTON, NO PILOT, BK	BLACK
3 BUTTONS	CPSD3W	CONTROL PANEL SWITCH, 3 BUTTON, NO PILOT, WH	WHITE
	CPSD3I	CONTROL PANEL SWITCH, 3 BUTTON, NO PILOT, IV	IVORY
	CPSD3LA	CONTROL PANEL SWITCH, 3 BUTTON, NO PILOT, LA	LIGHT ALMOND
	CPSD3GY	CONTROL PANEL SWITCH, 3 BUTTON, NO PILOT, GY	GRAY
	CPSD3BK	CONTROL PANEL SWITCH, 3 BUTTON, NO PILOT, BK	BLACK
4 BUTTONS	CPSD4W	CONTROL PANEL SWITCH, 4 BUTTON, NO PILOT, WH	WHITE
	CPSD4I	CONTROL PANEL SWITCH, 4 BUTTON, NO PILOT, IV	IVORY
	CPSD4LA	CONTROL PANEL SWITCH, 4 BUTTON, NO PILOT, LA	LIGHT ALMOND
	CPSD4GY	CONTROL PANEL SWITCH, 4 BUTTON, NO PILOT, GY	GRAY
	CPSD4BK	CONTROL PANEL SWITCH, 4 BUTTON, NO PILOT, BK	BLACK
6 BUTTONS	CPSD6W	CONTROL PANEL SWITCH, 6 BUTTON, NO PILOT, WH	WHITE
	CPSD6I	CONTROL PANEL SWITCH, 6 BUTTON, NO PILOT, IV	IVORY
	CPSD6LA	CONTROL PANEL SWITCH, 6 BUTTON, NO PILOT, LA	LIGHT ALMOND
	CPSD6GY	CONTROL PANEL SWITCH, 6 BUTTON, NO PILOT, GY	GRAY
	CPSD6BK	CONTROL PANEL SWITCH, 6 BUTTON, NO PILOT, BK	BLACK
	CPSD6BK	CONTROL PANEL SWITCH, 6 BUTTON, NO PILOT, BK	BLACK

NOTES:


- LOW VOLTAGE DEVICES: 24 VDC.  
POWERED BY CONTROL PANEL, ORDERED SEPARATELY)  
USING PLENUM RATED RJ45 UTP CABLE (CAT.# UTPxxOR,  
ORDERED SEPARATELY).
- FOR INDOOR USE ONLY,  
OPERATING TEMPERATURE: 32°F TO 104°F [0°C TO 40°C];  
RELATIVE HUMIDITY (NON-CONDENSING): 0 TO 95%.
- SWITCHES CAN BE MOUNTED TO SINGLE OR  
MULTI-GANG STANDARD WALL BOXES.
- ALL DIMENSIONS ARE IN INCHES [mm].

CAGE CODE 74545

1	NEW RELEASE PER DCN #23043 EMD	SL	4/18/17
REV	DESCRIPTION	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE IN INCHES [mm].

TITLE  
CONTROL PANEL DIMMING SWITCHES


**WIRING DEVICE-KELLEMS**  
**HUBBELL INCORPORATED**  
 SHELTON, CT

TOLERANCES UNLESS OTHERWISE SPECIFIED .XX = ± .01 .XXX = ± .005 ANGLE TOL. ±2°	DR. BY EMD	SCALE NTS
CHK. BY	DATE	4/18/17

B  
M-13610  
1