



CATALOG NUMBER	BOTTOM FEED CAT. NO.	BOTTOM FEED CONDUIT SIZES
S1R8PTFIT1	S1R8JNC1	1" & 1-1/2 EMT
S1R8PTFIT2	S1R8JNC2	(2) 1" EMT
S1R8PTFIT3	S1R8JNC3	2" EMT

- NOTES:
- 1) ALL DIMENSIONS ARE IN INCHES AND [MILLIMETERS]
 - 2) ALL DIMENSIONS ARE COMMON TO ALL CATALOG NUMBERS. BOTTOM FEED BOXES VARY AS SPECIFIED.
 3. ALL UNITS ARE SHIPPED WITH JUNCTION BOX SUB-ASSY (S1R8JNCBOX) SHIPPED LOOSELY. SEE M-11989 FOR DIMENSIONS.

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
CAN WELDMENT	STEEL	ZINC PLATE
INSTALLATION PLATE	STEEL	ZINC PLATE
SUB-PLATE MTG. PLATE	STEEL	WHITE PAINT
STANDOFFS	STNLS. STL.	--
FIRE BARRIER, UPPER	FIRE BAR. MATL.	NATURAL
FIRE BARRIER, LOWER	FIRE BAR. MATL.	NATURAL
WASHERS	FIBER	RED
MOUNTING SCREWS	STEEL	ZINC PLATE
DIVIDERS	STEEL	ZINC PLATE
SPACER	FIRE BAR. MATL.	BLACK
TAPE	PLASTIC	YELL./BLK.

NO.	DESCRIPTION	APP.	DATE
5	ADDED SHEET 2 PER DCN23387	AD	10/18/17
4	IN PARTS LIST- FOR STANDOFF "FINISH" -- WAS ZINC PLATE PER DCN 21112. MYA	PJB	4/8/15
3	UPDATED IMAGES DCN20245		12/13/13
2	UPDATED IMAGES DCN18755		4/13/12
1	RELEASED PER DCN18435		12/14/11

SYM	REVISIONS	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE SERVICE FITTING, FIRE RATED POKE THROUGH, 8 INCH DIAMETER

TOLERANCES UNLESS OTHERWISE SPECIFIED .XX = ±.01 .XXX = ±.005 ANGLES = ±2°	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT	
	DR. BY SRE	APP. BY
	TR. BY	SCALE 1:2
	CHK. BY	DATE 6/10/11

DIMENSION SHEET FOR CAT. NO. M-11921
 REPAIRABLE NON-REPAIRABLE

