



PUSH-IN CABLE CONNECTORS

Rugged one-piece design provides fast tool-free install!



NEW!

Applications

RACO's new Single and Double Barrel push-in cable connectors make it easy to secure two or more armoured cables into boxes or enclosures. Simply insert a cable into the cable opening, then snap the box end of the connector into a box knockout, done! No tools needed for a secure assembly. Single or Double Barrel Push-in connectors are perfect for new or rework and can be removed and reused.

Features

- Fits standard 1/2" knockouts in electrical boxes or enclosures
- Designed to terminate MC, MCI-A, AC, AC/HFC, MCI-A HFC, MC-PCS, RWFMC
- 40RACCN tinted blue and 4040RACCN tinted gold inside to indicate larger cable range
- Die-cast zinc construction with nylon anti-short bushing
- For use in dry locations only
- See back for cable ranges



38RACCN



40RACCN



3838RACCN



4040RACCN



Catalog No.	Description	Inner Carton Qty.	Inner Ctn I2 of 5	Ship Carton Qty.	Ship Carton I 2 of 5
38RACCN	3/8" Push-in Connector (1/2" KO)	50	30805035054698	500	50805035054692
40RACCN	3/8" Push-in Connector (1/2" KO)	50	30805035054704	500	50805035054708
3838RACCN	Two 3/8" Push-in Connectors (1/2"KO)	25	30805035054780	100	50805035054784
4040RACCN	Two 3/8" Push-in Connectors (1/2"KO)	25	30805035054797	100	50805035054791



CABLE RANGES & INSTRUCTIONS




38RACCN / 3838RACCN

Cable Type (Steel & Aluminum)	Cable Ranges	Cable Dimensions	
		Steel	Aluminum
MC	14/2 - 10-3	0.460 - 0.611 in. (12-16 mm)	0.402 - 0.570 in. (10-14 mm)
MCI-A			
AC/HCF			
MCI-A HCF	12/2 - 10-3		
MC-PCS (SOLID)	12/2 - 12-3		
RWFMC CONDUIT	3/8" (9.5mm) Trade Size Flex Anti Short Bushing Required		

40RACCN / 4040RACCN

Cable Type (Steel & Aluminum)	Cable Ranges	Cable Dimensions	
		Steel	Aluminum
MC	14/3 - 10-3	0.460 - 0.611 in. (12-16 mm)	0.402 - 0.570 in. (10-14 mm)
MCI-A			
AC			
AC/HCF	14/2 - 10-3		
MCI-A HCF	12/2 - 10-3		
MC-PCS (SOLID)	12/2 - 12-3		
RWFMC CONDUIT	3/8" (9.5mm) Trade Size Flex Anti Short Bushing Required		

38RACCN / 40RACCN / 3838RACCN / 4040RACCN CONNECTOR REMOVAL INSTRUCTIONS



HUBBELL CANADA
870 Brock Road South • Pickering, ON L1W 1Z8
1-800-465-7051
www.hubbell.ca



H3878-3838-4040_CANEN
rev 09/22