



M-14219

1



HBLFMPDD10xx SHOWN

NOTES:  
1) DIMENSIONS ARE INCHES[MM]

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
RACEWAY BASE	ALUMINUM	
RACEWAY COVER	ALUMINUM	SEE TABLE
FITTING CHASSIS	GALV. STEEL	
FITTING SIDES	ALUMINUM	
FITTING COVERS	THERMOPLASTIC	
FITTING TOP	STEEL	POWDER COAT
SCREWS (EXT)	STEEL	BLACK
SCREWS (INT)	STEEL	ZINC PLATED

DIMENSION SHEET FOR CAT. NO. SEE TABLE

1	RELEASED PER DCN#191120105745	EMD	11/20/19
REV	DESCRIPTION	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE IN INCHES [mm].

TITLE  
FLOOR MOUNTED RACEWAY, 1-2-3 KIT

CAT NO	DESCRIPTION	CONFIGURATION	FINISH
HBLFMPDD10DG	ON FLR KIT,5-15R,10'C,1'2'3'TRK,DK G	2 DUPLEX, 10 FT CORD	DARK GRAY
HBLFMPDD10A	ON FLR KIT,5-15R,10'C,1'2'3'TRK,AL	2 DUPLEX, 10 FT CORD	ALUMINUM
HBLFMPDD15DG	ON FLR KIT,5-15R,15'C,1'2'3'TRK,DK G	2 DUPLEX, 15 FT CORD	DARK GRAY
HBLFMPDD15A	ON FLR KIT,5-15R,15'C,1'2'3'TRK,AL	2 DUPLEX, 15 FT CORD	ALUMINUM
HBLFMPUD10DG	ON FLR KIT,USB,5-15R,10'C,1'2'3'TRK,DK G	1 DUPLEX + 1 USB RECP, 10 FT CORD	DARK GRAY
HBLFMPUD10A	ON FLR KIT,USB,5-15R,10'C,1'2'3'TRK,AL	1 DUPLEX + 1 USB RECP, 10 FT CORD	ALUMINUM
HBLFMPUD15DG	ON FLR KIT,USB,5-15R,15'C,1'2'3'TRK,DK G	1 DUPLEX + 1 USB RECP, 15 FT CORD	DARK GRAY
HBLFMPUD15A	ON FLR KIT,USB,5-15R,15'C,1'2'3'TRK,AL	1 DUPLEX + 1 USB RECP, 15 FT CORD	ALUMINUM

	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT	
	DR. BY EMD	SCALE 1/2
TOLERANCES UNLESS OTHERWISE SPECIFIED .XX = ±.01 .XXX = ±.005 ANGLE TOL. ±2'	CHK. BY	DATE 11/13/19