

CONTEMPORARY CONCRETE BOLLARDS



Exclusive
LED Ring
Technology

Striking Modern Forms

Four Sizes, Round and Square



NEW LED

ARCHITECTURAL AREA LIGHTING

Contemporary Concrete Bollards

NEW LED MODELS



Cool Top

Sturdy concrete cap is safe for close contact with children and pets

Long Lasting

Newest LED technology for bright, efficient illumination

Rugged Grill

Cast aluminum, available in 13 standard colors

Heavy-Duty


Precast concrete with internal steel reinforcement

Round Contemporary Bollards

Available in 9", 12", or 18" diameter

Square Contemporary Bollards

Available in 9", 12", or 16" square




CB12R



CB18R-24-HORZ-FLAT-MSB


Grill Styles

AAL's Contemporary Concrete Bollards are available in three grill styles to meet various lighting design needs. Choose between cutoff, horizontal, or vertical and select an LED source to maximize life and reduce energy consumption.



Top Styles

Choose between three top styles to complement the architecture of the site. Round Contemporary Bollards are available with flat or dome tops and Square Contemporary Bollards are available with flat or pyramid tops.



Mounting Options

AAL's Contemporary Concrete Bollards offer installation flexibility, with internal or external mounting available (external only for CB9 models).

Contemporary Concrete Bollards

NEW LED MODELS



9" ROUND AND SQUARE BOLLARD

ROUND	OAH (inches)	GRILL	TOP STYLE
CB9R	24	CUTOFF	FLAT
CB9R	36	CUTOFF	FLAT
CB9R	42	CUTOFF	FLAT
CB9R	24	CUTOFF	DOME
CB9R	36	CUTOFF	DOME
CB9R	42	CUTOFF	DOME

SQUARE	OAH (inches)	GRILL	TOP STYLE
CB9S	24	CUTOFF	FLAT
CB9S	36	CUTOFF	FLAT
CB9S	42	CUTOFF	FLAT
CB9S	24	CUTOFF	PYRM
CB9S	36	CUTOFF	PYRM
CB9S	42	CUTOFF	PYRM

Grill assembly for CB9 models is 8"/203mm square or DIA.

12" ROUND AND SQUARE BOLLARD

ROUND	OAH (inches)	GRILL	TOP STYLE
CB12R	24	CUTOFF	FLAT
CB12R	36	CUTOFF	FLAT
CB12R	42	CUTOFF	FLAT
CB12R	26	CUTOFF	DOME
CB12R	38	CUTOFF	DOME
CB12R	44	CUTOFF	DOME
CB12R	24	HORZ	FLAT
CB12R	36	HORZ	FLAT
CB12R	42	HORZ	FLAT
CB12R	26	HORZ	DOME
CB12R	38	HORZ	DOME
CB12R	44	HORZ	DOME
CB12R	24	VERT	FLAT
CB12R	36	VERT	FLAT
CB12R	42	VERT	FLAT
CB12R	24	VERT	DOME
CB12R	36	VERT	DOME
CB12R	42	VERT	DOME

SQUARE	OAH (inches)	GRILL	TOP STYLE
CB12S	24	HORZ	FLAT
CB12S	36	HORZ	FLAT
CB12S	42	HORZ	FLAT
CB12S	24	HORZ	PYRM
CB12S	36	HORZ	PYRM
CB12S	42	HORZ	PYRM
CB12S	24	VERT	FLAT
CB12S	36	VERT	FLAT
CB12S	42	VERT	FLAT
CB12S	24	VERT	PYRM
CB12S	36	VERT	PYRM
CB12S	42	VERT	PYRM

LAMP/BALLAST

27LED-WW	27 light emitting diode array (28 watt). Warm white (3500K). IES Type 5. 120 thru 277 volt. CB9 models only.
27LED-BW	27 light emitting diode array (28 watt). Bright white (5100K). IES Type 5. 120 thru 277 volt. CB9 models only.
36LED-WW	36 light emitting diode array (37 watt). Warm white (3500K). IES Type 5. 120 thru 277 volt. CB12 models only.
36LED-BW	36 light emitting diode array (37 watt). Bright white (5100K). IES Type 5. 120 thru 277 volt. CB12 models only.

LEDs and drivers included. All fixtures prewired for 277 volts, unless specified. All applicable ballasts are EISA compliant.

CONCRETE FINISH

MSB	Medium sandblast, natural color finish
AGR	Exposed aggregate finish

GRILL COLOR

All standard and premium AAL colors available for grill.
For RAL and custom colors, please submit a 4-digit RAL number or color chip for custom colors.

OPTIONS

HSS	House side shield -180°
RBC	A single gang junction box, cast in place, weather proof cover only. Consult factory for location.
Colored Concrete	Based on Davis colors. For custom color and aggregate, customer must provide aggregate, sand, and colorant.

MOUNTING

INT	Internal mounting. Not available with CB9 models.
EXT	External mounting

Ordering Information Example	BOLLARD	OAH	GRILL	TOP STYLE	LAMP/BALLAST	CONCRETE FINISH	GRILL COLOR	OPTIONS	MOUNTING
	CB9R	36	CUTOFF	DOME	27LED-WW	MSB	BLK	HSS	EXT
CB12S	36	VERT	PYRM	36LED-WW	AGR	BLK	RBC	INT	

Refer to AAL's Contemporary Concrete Bollard brochure for photometry and complete specification and ordering details.

Contemporary Concrete Bollards



16" SQUARE BOLLARD

SQUARE	OAH (inches)	GRILL	TOP STYLE
CB16S	24	HORZ	FLAT
CB16S	36	HORZ	FLAT
CB16S	42	HORZ	FLAT
CB16S	24	HORZ	PYRM
CB16S	36	HORZ	PYRM
CB16S	42	HORZ	PYRM
CB16S	24	VERT	FLAT
CB16S	36	VERT	FLAT
CB16S	42	VERT	FLAT
CB16S	24	VERT	PYRM
CB16S	36	VERT	PYRM
CB16S	42	VERT	PYRM
CB16S	24	CUTOFF	FLAT
CB16S	36	CUTOFF	FLAT
CB16S	42	CUTOFF	FLAT
CB16S	24	CUTOFF	PYRM
CB16S	36	CUTOFF	PYRM
CB16S	42	CUTOFF	PYRM

18" ROUND BOLLARD

ROUND	OAH (inches)	GRILL	TOP STYLE
CB18R	24	CUTOFF	FLAT
CB18R	36	CUTOFF	FLAT
CB18R	42	CUTOFF	FLAT
CB18R	29	CUTOFF	DOME
CB18R	41	CUTOFF	DOME
CB18R	47	CUTOFF	DOME
CB18R	24	HORZ	FLAT
CB18R	36	HORZ	FLAT
CB18R	42	HORZ	FLAT
CB18R	29	HORZ	DOME
CB18R	41	HORZ	DOME
CB18R	47	HORZ	DOME
CB18R	24	VERT	FLAT
CB18R	36	VERT	FLAT
CB18R	42	VERT	FLAT
CB18R	27	VERT	DOME
CB18R	39	VERT	DOME
CB18R	45	VERT	DOME

LAMP/BALLAST

54LED-WW	54 light emitting diode array (55 watt). Warm white (3500K). IES Type 5. 120 thru 277 volt. CB16S only.
54LED-BW	54 light emitting diode array (55 watt). Bright white (5100K). IES Type 5. 120 thru 277 volt. CB16S only.
72LED-WW	72 light emitting diode array (74 watt). Warm white (3500K). IES Type 5. 120 thru 277 volt. CB18R only.
72LED-BW	72 light emitting diode array (74 watt). Bright white (5100K). IES Type 5. 120 thru 277 volt. CB18R only.

LEDs and drivers included. All fixtures prewired for 277 volts, unless specified. All applicable ballasts are EISA compliant.

CONCRETE FINISH

MSB	Medium sandblast, natural color finish
AGR	Exposed aggregate finish

GRILL COLOR

All standard and premium AAL colors available for grill.
For RAL and custom colors, please submit a 4-digit RAL number or color chip for custom colors.

OPTIONS

HSS	House side shield -180°
RBC	A single gang junction box, cast in place, weather-proof cover only. Consult factory for location.
Colored Concrete	Based on Davis colors. For custom color and aggregate, customer must provide aggregate, sand, and colorant.

MOUNTING

INT	Internal mounting
EXT	External mounting

Ordering Information Example

BOLLARD	OAH	GRILL	TOP STYLE	LAMP/BALLAST	CONCRETE FINISH	GRILL COLOR	OPTIONS	MOUNTING
CB16S	36	HORZ	FLAT	54LED-WW	MSB	BLK	HSS	EXT
CB18R	29	CUTOFF	DOME	72LED-WW	AGR	BLK	RBC	INT

Refer to AAL's Contemporary Concrete Bollard brochure for photometry and complete specification and ordering details.



16555 East Gale Ave.
City of Industry | CA 91745
T 626.968.5666 | F 626.369.2695
www.aal.net

