


CFP

Edge-lit Flat Panel

The CFP offers edge-lit LED technology in a sleek, modern, flat panel design. Light classrooms, offices, medical facilities, cleanrooms and general public spaces using edge-to-edge illumination, without pixelation or bright spots.



Smooth, narrow frame



1x4, 2x2, and 2x4 sizes



Emergency Backup Compatible





CFP

An attractive, cost-effective, and reliable flat panel family.



- ▶ IC rated
- ▶ 80+ CRI
- ▶ 120-277V
- ▶ -20°C to +40°C
- ▶ 0-10V dimming
- ▶ Cleanroom suitable
- ▶ 5 year warranty
- ▶ T-bar clips for secure mounting
- ▶ 60,000 hour LEDs at L70 (up to 180,000 projected life)
- ▶ DLC® (DesignLights Consortium) Qualified, with some Premium Qualified configurations - see www.designlights.org

Catalog Number	Description	Lumens	Watts	LPW	Qty on Pallet
CFP14-4035¹	1x4 Edge-Lit Flat Panel, 4000lm 3500K	3951	39	101	51
CFP14-4040¹	1x4 Edge-Lit Flat Panel, 4000lm 4000K	4102	39	105	51
CFP22-3335¹	2x2 Edge-Lit Flat Panel, 3300lm, 3500K	3382	32	106	40
CFP22-3335-HE²	2x2 Edge-Lit Flat Panel, 3300lm, 3500K, High Efficacy	3299	26	125	40
CFP22-3340¹	2x2 Edge-Lit Flat Panel, 3300lm, 4000K	3475	32	109	40
CFP22-3340-HE²	2x2 Edge-Lit Flat Panel, 3300lm, 4000K, High Efficacy	3430	27	127	40
CFP22-4035¹	2x2 Edge-Lit Flat Panel, 4000lm, 3500K	4302	41	105	40
CFP22-4040¹	2x2 Edge-Lit Flat Panel, 4000lm, 4000K	4074	40	102	40
CFP24-4135¹	2x4 Edge-Lit Flat Panel, 4100lm, 3500K	4307	40	107	20
CFP24-4135-HE²	2x4 Edge-Lit Flat Panel, 4100lm, 3500K, High Efficacy	4229	34	124	20
CFP24-4140¹	2x4 Edge-Lit Flat Panel, 4100lm, 4000K	4123	40	103	20
CFP24-4140-HE²	2x4 Edge-Lit Flat Panel, 4100lm, 4000K, High Efficacy	4334	34	127	20
CFP24-5535¹	2x4 Edge-Lit Flat Panel, 5500lm, 3500K	5447	49	110	20
CFP24-5540¹	2x4 Edge-Lit Flat Panel, 5500lm, 4000K	5608	50	112	20

¹ DLC® (DesignLights Consortium) Qualified - see www.designlights.org

² DLC® (DesignLights Consortium) Premium Qualified - see www.designlights.org

Accessories (Order Separately)	
PLD10M	Dual-Lite® Emergency LED Battery Pack, field installed
FK14	1' x 4' Single Flange Kit
FK22	2' x 2' Single Flange Kit
FK24	2' x 4' Single Flange Kit
CFPSMK-14	1' x 4' CFP Surface Mount Kit
CFPSMK-22	2' x 2' CFP Surface Mount Kit
CFPSMK-24	2' x 4' CFP Surface Mount Kit
CFPCM36YSC5F-KIT	36" Cable Mount Kit for 1' or 2' wide Cable Mount fixtures, 5 Wire

