



# Low Voltage Distribution Transformer - Single Phase, 240X480 - 120/240V, 7.5kVA

By Acme Electric  
Catalog # T2535153S



Low Voltage Distribution Transformer - Single Phase, 240X480 - 120/240V, 7.5kVA

## Features

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

## General

|                      |                                   |
|----------------------|-----------------------------------|
| ANFC Taps            | 2                                 |
| BNFC Taps            | 2                                 |
| Catalog Number       | T2535153S                         |
| Construction         | Encapsulated                      |
| Electrostatic Shield | Shielded                          |
| Max Temperature Rise | 115 Degrees Celsius               |
| Mounting Type        | Wall                              |
| Primary Voltage      | 240 X 480                         |
| Product Category     | Dry Type Distribution Transformer |
| Secondary Voltage    | 120/240 V                         |
| Taps % Steps         | 2.5%                              |
| UL Insulation Class  | 180°C                             |
| UPC                  | 047503734056                      |
| Winding Material     | AL                                |
| kVA                  | 7.5                               |

## Dimensions

|            |                               |
|------------|-------------------------------|
| Dimensions | 10.84 in x 13.5 in x 15.19 in |
| Height     | 15.19 in                      |
| Length     | 10.84 in                      |
| Weight     | 115 lb                        |
| Width      | 13.5 in                       |

## Electrical Ratings

|                  |             |
|------------------|-------------|
| Frequency Rating | 60 Hz       |
| Primary Voltage  | 240 X 480 V |

## Certifications And Compliance

|              |              |
|--------------|--------------|
| CSA Standard | C22.2 No. 47 |
| Nema Rating  | NEMA 3R      |
| UL Standard  | UL 506       |

## Logistics

|                 |   |
|-----------------|---|
| Carton Quantity | 1 |
| Pallet Quantity | 6 |

## Product Assets

- [Brochures - General Purpose Dry-Type Distribution Transformers](#)
- [Catalogs - Acme Electric Catalog - Section 1 - Dry-Type Distribution Transformers](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Customer Use Drawings - a-125873](#)
- [Customer Use Drawings - a-125881](#)
- [Customer Use Drawings - a-125883](#)
- [Customer Use Drawings - a-125893](#)
- [Customer Use Drawings - a-102722-b](#)
- [Customer Use Drawings - a-125877](#)
- [Customer Use Drawings - a-700322](#)
- [Customer Use Drawings - a-125885](#)
- [Customer Use Drawings - a-125852](#)
- [Engineering Drawing - T2535153S](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
ACME-T2535153S-SPEC-EN | REV 6/2024