



# Low Voltage Distribution Transformer - Single Phase, 190/208/220/240 X 380/416/440/480 - 120/240V, 2kVA

By Acme Electric  
Catalog # [TF279261S](#)



Low Voltage Distribution Transformer - Single Phase,  
190/208/220/240 X 380/416/440/480 - 120/240V, 2kVA

## Features

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

## General

|                      |   |
|----------------------|---|
| CE Compliant         | CE Marked                                       |
| Catalog Number       | TF279261S                                       |
| Construction         | Encapsulated                                    |
| Electrostatic Shield | Shielded  |
| Max Temperature Rise | 115 Degrees Celsius                             |
| Mounting Type        | Wall  |
| Primary Voltage      | 190 / 208 / 220 / 240 X 380 / 416 / 440 / 480 V |
| Product Category     | Dry Type Distribution Transformer               |
| Secondary Voltage    | 120/240 V                                       |
| UL Insulation Class  | 180°C   |
| UPC                  | 047503400029                                    |
| Winding Material     | CU  |
| kVA                  | 2   |

## Dimensions

|            |                          |
|------------|--------------------------|
| Dimensions | 5.13 in x 5.5 in x 13 in |
| Height     | 13 in                    |
| Length     | 5.13 in                  |
| Weight     | 38 lb                    |
| Width      | 5.5 in                   |

## Electrical Ratings

|                  |                                     |
|------------------|-------------------------------------|
| Frequency Rating | 50/60 Hz                            |
| Primary Voltage  | 190/208/220/240 X 380/416/440/480 V |

## Certifications And Compliance

|              |              |
|--------------|--------------|
| CE Compliant | CE Marked    |
| CSA Standard | C22.2 No. 47 |
| Nema Rating  | NEMA 3R      |
| UL Standard  | UL 506       |

## Logistics

|                 |    |
|-----------------|----|
| Carton Quantity | 1  |
| Pallet Quantity | 36 |

## Product Assets

[Brochures - General Purpose Dry-Type Distribution Transformers](#)  
[Catalogs - Acme Electric Catalog - Section 1 - Dry-Type Distribution Transformers](#)  
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)  
[Engineering Drawing - TF279261S](#)  
[SDS - HCC SDS](#)  
[Specifications - TF279261S Specification Sheet English](#)  
[Specifications - TF279261S Specification Sheet French](#)  
[Specifications - TF279261S](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved  
ACME\_CA-TF279261S-SPEC-EN | REV 4/2025