

Suspension Clamp

By ANDERSON
Catalog # [HAS62C](#)

"The HAST2 suspension clamp is a double groove, saddle type suspension clamp designed for use on standard voltage T2 transmission lines. Type HAST2 is recommended for AAC, ACSR, or AAAC T2 conductors. Maximum conductor temperature 130°C. Material: Clamp-Aluminum alloy, Clevis-Galvanized Ductile iron. Clamping Range: 0.977"-1.165"



*Representative Image

Features

- "Bolt and nut may be substituted for clevis pin by adding suffix "BNK" to catalog number
- The clevis bolt and clevis pin are the same diameter
- "C" suffix indicates the suspension clamp will contain the clevis eye CA04"

General

Bolt Installation Torque (Recommended)	480 in-lbs
EU RoHS Indicator	No
Fitting Type	Clevis
Material - Clamp	Aluminum
Material - Hardware	Galvanized Steel
Material - Pin	Stainless Steel
Material - Pin (Cotter)	Stainless Steel
Material - Socket and Clevis	Galvanized Ductile Iron
Product Category	Suspension Clamp
Strength Rating - Ultimate Body	17000 lb
Type	Standard Voltage Suspension Clamps
U-Bolts	1/2 in
UPC	096359315124

Dimensions

Angle - Take-Off Maximum	30 °
Clamping - Maximum	0.62 in
Clamping - Minimum	0.2 in
Clevis Opening	2.28125 in
Diameter - Clevis Pin	0.625 in
Height	2.28125 in
Length	6.75 in
Weight	3.5 lb

Electrical Ratings

Voltage Application	Standard
---------------------	----------

Conductor Related

Clamping Range	0.2- 0.62
Conductor Compatibility	ACSR-Turkey-6-6/1;ACSR-Swan-4-6/1;ACSR-Swanate-4-7/1;ACSR-Sparrow-2-6/1;ACSR-Sparate-2-7/1;ACSR-Robin-1-6/1;ACSR-Raven-1/0-6/1;ACSR-Quail-2/0-6/1;ACSR-Pigeon-3/0-6/1;ACSR-Penguin-4/0-6/1;ACSR-Waxwing-266.8-18/1;AAC-Peachbell-6-7;AAC-Rose-4-7;AAC-Iris-2-7;AAC-Pansy-1-7;AAC-Poppy-1/0-7;AAC-Aster-2/0-7;AAC-Phlox-3/0-7;AAC-Oxlip-4/0-7;AAC-Valerian-250-19;AAC-Laurel-266.8-19;AAAC 6201 Alloy-Akron-30.58-6/18;AAAC 6201 Alloy-Alton-48.69-6/18;AAAC 6201 Alloy-Ames-77.47-6/18;AAAC 6201 Alloy-Azusa-123.3-6/18;AAAC 6201 Alloy-Anaheim-155.4-6/18;AAAC 6201 Alloy-Amherst-195.7-6/18;AAAC 6201 Alloy-Alliance-246.9-6/18

Logistics

Pallet Quantity	270
-----------------	-----

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)
[Literature - Ropes Course Industry Letter \(April 2021\)](#)
[Sales Drawings - HAS Product Family](#)
[Technical Solutions - AN-HAS62C-SPEC-EN](#)

