

# HUBBELL

## Power Systems

### Connector, Parallel Groove

By ANDERSON  
Catalog # [LCC111XB](#)

Two U-Bolt Aluminum Parallel Groove Connector



\*Representative Image

#### Features

- For aluminum to copper conductor connections only
- Sealant (XB) is recommended on all connections

#### General

Bolt Head Type	U-Bolt
Bolt Installation Torque (Recommended)	0 ft-lbs
Catalog Number	LCC111XB
Cover Available	No
EU RoHS Indicator	No
Material	Aluminum
Material - Body	Aluminum Alloy
Material - Body Halves	Aluminum Alloy
Material - Bolt	Galvanized Steel
Material - Bottom Member	Copper Alloy
Material - Casting	Aluminum Alloy
Material - Hardware	Galvanized Steel
Material - Spacer	Aluminum Alloy, Copper Lined
Plating	No
Product Category	Mechanical Connectors
Style	Two U-Bolt
UPC	096359320098

#### Dimensions

Bolt Diameter	0.5
Diameter - Bolt	0.5 in
Weight	0.882 lb

#### Conductor Related

Conductor Compatibility	ACSR-Turkey-6-6/1;ACSR-Swan-4-6/1;ACSR-Swanate-4-7/1;ACSR-Sparrow-2-6/1;ACSR-Sparate-2-7/1;ACSR-Robin-1-6/1;ACSR-Raven-1/0-6/1;ACSR-Quail-2/0-6/1;AAC-Peachbell-6-7;AAC-Rose-4-7;AAC-Iris-2-7;AAC-Pansy-1-7;AAC-Poppy-1/0-7;AAC-Aster-2/0-7;AAAC 6201 Alloy-Akron-30.58-6/18;AAAC 6201 Alloy-Alton-48.69-6/18;AAAC 6201 Alloy-Ames-77.47-6/18;AAAC 6201 Alloy-Azusa-123.3-6/18
Conductor Diameter (Tap) - Maximum	0.447 in
Conductor Diameter (Tap) - Minimum	0.128 in
Conductor Diameter - Maximum	0.447 in
Conductor Diameter - Minimum	0.162 in
Conductor Diameter Range	0.162 - 0.447

#### Certifications And Compliance

UL Listed	No
-----------	----

#### Logistics

Pallet Quantity	2304
-----------------	------

#### Product Assets

[Catalogs - Distribution Connectors](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
AN-LCC111XB-SPEC-EN | REV 6/2024