

Aluminum Compression Terminal
for 550 - 600 AL, 477 24/7, 26/7,
556.5 36/1, 18/1 ACSR, 650 - 700
COMPACT

By ANDERSON
Catalog # [VAUL60012BN](#)



*Representative Image

Aluminum Compression Terminal for 550 - 600 AL, 477 24/7,
26/7, 556.5 36/1, 18/1 ACSR, 650 - 700 COMPACT

Features

Connectors are prefilled with rubber compatible inhibitor and sealed with color coded end caps.

General

Catalog Number	VAUL60012BN
Color Code	None
Crimp Method	VERSAtile™ (Accommodates Conventional And Anderson Tools)
Die Size	*See Resources / Downloads for die selection and installation instructions
Material	Aluminum
Material - Body	Aluminum
Number of Pad Holes	2
Physical Attribute - Number of Holes	2
Plating	No
Style	Impact Extruded
UPC	096359334958

Dimensions

Diameter - Pad Bolt	0.5 in
Dimension - Hole Size inch	0.500 in
Weight	0.608 lb

Conductor Related

Conductor Compatibility	ACSR-Waxwing-266.8-18/1;ACSR-Partridge-266.8-26/7;ACSR-Ostrich-300-26/7;ACSR-Merlin-336.4-18/1;ACSR-Linnet-336.4-26/7;ACSR-Oriole-336.4-
-------------------------	--

30/7;ACSR-Chickadee-397.5-18/1;ACSR-Brant-397.5-24/7;ACSR-Ibis-397.5-26/7;ACSR-Lark-397.5-30/7;ACSR-Pelican-477-18/1;ACSR-Flicker-477-24/7;ACSR-Hawk-477-26/7;ACSR-Hen-477-30/7;ACSR-Osprey-556.5-18/1;ACSR-Brahma-203.2-16/19;AAC-Tulip-336.1-19;AAC-Daffodil-350-19;AAC-Canna-397.5-19;AAC-Cosmos-477-19;AAC-Syringa-477-37;AAC-Zinnia-500-19;AAC-Hyacinth-500-37;AAC-Dahlia-556.5-19;AAC-Mistletoe-556.5-37;AAC-Meadowsweet-600-37

Conductor Diameter (VersaCrimp) - Maximum	0.879 in
Conductor Diameter (VersaCrimp) - Minimum	0.609 in

Certifications And Compliance

UL Listed	No
-----------	----

Logistics

Carton Quantity	40
-----------------	----

Product Assets

- [Catalogs - Distribution Connectors](#)
- [Installation Manuals - VAUL Terminals Installation Procedures](#)
- [Sales Drawings - VAULxxx_drawing](#)
- [Specifications - VAUL60012BN](#)