



2.4/5/6 GHZ 8/10/10 DBI 14 ELEMENT INDOOR PATCH ANTENNA WITH MPC ATS-03951 (ATS-OP-2456-81010-14MPC-36)



ELECTRICAL SPECIFICATIONS

Frequency Range: 2.4-2.48/5.15-5.85/5.925-7.125 GHz
Gain: 8/10/10dBi
Polarization: 7 Vertical / 7 Horizontal
Horizontal Beamwidth: 65°/40°/35°
Vertical Beamwidth: 65°/40°/35°
VSWR: <1.5:1 Max: 2.0
Isolation: >30dB
Impedance: 50 Ω



MECHANICAL SPECIFICATIONS

Dimensions: 15.35" x 15.35" x 2.25" (390x390x57mm)
Weight: 3 lb (1.3kg)
Number of Leads: 14
Connector: 4MPC (5GHz), 6MPC-BLK (6GHz and Scan), 6MPC-WHT (2.4/5/GHz)
Installation: Flush Mount to Wall or Articulating
Wall/Pole Mount (Included)

Cable Length: 36" (910mm)
Cable Type: ATS-100
Radome Material: ABS



ENVIRONMENTAL SPECIFICATIONS

Installation Environment: Indoor or Outdoor
IP Rating: IP66

WARRANTY

2 Year Limited Warranty





2.4/5/6 GHZ 8/10/10 DBI 14 ELEMENT INDOOR PATCH ANTENNA WITH MPC ATS-03951 (ATS-OP-2456-81010-14MPC-36)



VERTICAL
6 GHZ RADIO (6MPC-BLK)



HORIZONTAL

Frequency (MHz)	5900.0	6050.0	6150.0	6250.0	6350.0	6450.0	6550.0	6650.0	6750.0	6850.0	6950.0	7050.0	7125.0
Gain (dBi)	9.80	9.97	10.08	9.97	10.02	9.98	10.23	10.57	10.12	9.88	10.31	10.45	10.09



5 GHZ RADIO (4MPC)

Frequency (MHz)	4900.0	5000.0	5100.0	5150.0	5250.0	5350.0	5450.0	5550.0	5650.0	5750.0	5850.0
Gain (dBi)	9.13	9.53	9.63	9.32	9.64	9.72	9.93	9.70	9.61	9.62	9.70





2.4/5/6 GHZ 8/10/10 DBI 14 ELEMENT INDOOR PATCH ANTENNA WITH MPC ATS-03951 (ATS-OP-2456-81010-14MPC-36)





**VERTICAL
TRIBAND RADIO (6MPC-WHT)**

HORIZONTAL

Frequency (MHz)	2400.0	2420.0	2440.0	2460.0	2484.0
Gain (dBi)	7.96	8.01	8.02	8.16	8.46

Frequency (MHz)	5150.0	5250.0	5350.0	5450.0	5550.0	5650.0	5750.0	5850.0
Gain (dBi)	9.06	9.44	9.33	9.30	10.01	9.88	9.97	9.54

Frequency (MHz)	5925.0	6050.0	6150.0	6250.0	6350.0	6450.0	6550.0	6650.0	6750.0	6850.0	6950.0	7050.0	7125.0
Gain (dBi)	9.47	9.96	10.00	9.29	9.13	9.14	9.36	9.81	9.92	9.63	9.83	9.32	9.12





2.4/5/6 GHZ 8/10/10 DBI 14 ELEMENT INDOOR
PATCH ANTENNA WITH MPC
ATS-03951 (ATS-OP-2456-81010-14MPC-36)

