



Behavioral Health Surface-Mount VoIP Telephone (Auto-dial)

By Austdac
Catalog # 210-712BH

GAI-Tronics Behavioral Health series of rugged telephones are designed for use in environments where conversation privacy is desired but safety is a concern. The Model 210-712BH (Auto-dial) Surface-mount Handset Telephone is equipped with a shortened, 12-inch handset cord to prevent the handset being used as a weapon. The cord is also short enough to prevent the possibility of strangulation. Its rugged design provides both quality and longevity. The Model 210-702BH is a SIP-compatible telephone that is ideally suited for installation in any area requiring the Americans with Disabilities Act maximum protrusion Depth of 4 inches (corridors, hallways, passageways) or on any flat surface. The unit's rear mounting plate provides telephone line access, eliminating visibility of, or access to, cabling. Additionally, the 210-702BH is secured with security hardware to prevent vandalism.



Application

- Rehabilitation Centers
- Correctional Facilities
- Mental Health Facilities

General

Catalog Number	210-712BH
Color	Silver
Connectivity Options	VoIP
Material	Stainless Steel, Type 304, 14 Gauge, Brushed Finish
Mount location	Surface-Mount
Operating Temperature	-4°F to +131°F / -20°C to +55°C
Signal Type	VoIP - SIP
Specifications	UL/CSA, FCC
Storage Temperature Range	-40° C to +70° C
Temperature Rating	-4°F to +131°F (-20°C to +55°C)
Type	Auto-Dial
Weather Rating	Indoor

Dimensions

Cubic Capacity	58.81095 cu.in
----------------	----------------

Depth	3.27 in
Dimensions	10.0 in x 5.5 in x 3.27 in
Height	3.27 in
Length	10 in
Weight	5.5 lb
Width	5.5 in

Electrical Ratings

Signal	Ethernet
Voltage Rating Description	24-48 VDC or PoE

Certifications And Compliance

Certification	UL/CSA/FCC
Certified Listed	UL/CSA/FCC
Compliance	FCC CRF 47 Part 15

Product Assets

- [Brochures - Behavioral Health Telephones](#)
- [Brochures - Rugged Telephone Brochure](#)
- [Configuration Guide - VoIP Telephone Basic Configuration Guide](#)
- [Configuration Guide - VoIP Telephone Configuration Guide:](#)
- [Firmware versions 1193 Telephones \(v1.08\); 1201 Telephones for Auteldac 6 \(v1.08\)](#)
- [Literature - Behavioral Health Surface-mount VoIP Telephones](#)