



14x12x6 Heated PoE Enclosure with Cord Grip

By AccelTex Solutions
Catalog # [ATS-00263](#)



ATS-00263 (former catalog number ATS-14126P-S-L-CG-POE-H). The AccelTex Solutions Heated PoE enclosure allows an access point to be installed in an outdoor or other temperature-limiting environment. The heater and AP are powered by a single PoE cable run from the network switch

Features

- Heated PoE enclosure enables AP installations in outdoor or temperature-limiting environments
- Powers heater and AP through a single PoE cable for simplified setup

Application

Indoor Wi-Fi, Outdoor Wi-Fi

General

Catalog Number	ATS-00263
Color	Grey
Compatibility	• Arista C-230 • Arista C-230E • Arista C-330 • Arista C-360 • Arista C-460 • Arista C-460E • Arista O-105E • Arista O-235 • Arista O-235E • Aruba/HP AP-504 • Aruba/HP AP-505 • Aruba/HP AP-514 • Aruba/HP AP-515 • Aruba/HP AP-518 • Aruba/HP AP-534 • Aruba/HP AP-535 • Aruba/HP AP-555 • Aruba/HP AP-565 • Aruba/HP AP-567 • Aruba/HP AP-615 • Aruba/HP AP-635 • Aruba/HP AP-655 • Aruba/HP AP-735 • Aruba/HP AP-755 • Cisco Catalyst 9105AXI • Cisco Catalyst 9115i • Cisco Catalyst 9115e • Cisco Catalyst 9117

	• Cisco Catalyst 9120AXI • Cisco Catalyst 9120AXE • Cisco Catalyst 9120AXP • Cisco Catalyst 9124AXD • Cisco Catalyst 9124AXE • Cisco Catalyst 9124AXI • Cisco Catalyst 9130AXE • Cisco Catalyst 9130AXI • Cisco Catalyst 9136i • Cisco CW9162 • Cisco CW9164 • Cisco CW9166 • Cisco IW9167E • Cisco MR46 • Cisco MR46E • Cisco MR56 • Cisco MR57 • Cisco MR76 • Cisco MR86 • Mist AP24 • Mist AP32 • Mist AP32e • Mist AP33 • Mist AP43 • Mist AP43e • Mist AP45 • Mist AP45E • Mist AP47 • Mist AP47D • Mist AP47E • Mist AP63 • Mist AP63E
Cord Grip	Yes
Door Type	Solid
Enclosure Size	14x12x6
Enclosure Style	Mounting Feet
Enclosure System Components	14"x12"x6" Poly Enclosure with Solid Door, latch-lock10-gbps-ethernet-surge-suppressor-for-802-3at-af-bt60w-poe-injector12-vdc-15w-heaterdc-adjustable-thermostatn-style-

Cord Grip	Yes
Door Type	Solid
Enclosure Size	14x12x6
Enclosure Style	Mounting Feet
Enclosure System Components	14"x12"x6" Poly Enclosure with Solid Door, latch-lock10-gbps-ethernet-surge-suppressor-for-802-3at-af-bt60w-poe-injector12-vdc-15w-heaterdc-adjustable-thermostatn-style-

	bulkhead-jack-to-plug- lightning-arrestorcord- gripblank-backp
Environmental Conditions	Heated
Indoor/Outdoor	Indoor or Outdoor
Lock Type	Latch
Material	Polycarbonate
Operating Temperature	-20 to 60 °C
Technology	802.11ax, 802.3af, 802.3at, 802.3bt
UPC	662620432656

Dimensions

Dimensions	14 in x 12 in x 6 in
Height	6 in
Length	14 in
Width	12 in

Certifications And Compliance

Ratings	NEMA 3R
---------	---------

Product Assets

[Specifications - Specification Sheet](#)



A Hubbell brand