



24x24x10 Polycarbonate Enclosure with Solid Door, Key Lock and No Holes

By AccelTex Solutions
Catalog # [ATS-00416](#)



ATS-00416 (former catalog number ATS-242410P-S-K-NH-BBP). The AccelTex Solutions polycarbonate enclosure protects any enterprise-class AP from environmental threats and tampering. Purpose built for enterprise applications, this aesthetically pleasing enclosure is inconspicuous in an indoor application and durable enough to provide NEMA 6P protection in an outdoor environment.

Features

- Polycarbonate enclosure protects enterprise-class APs from environmental threats and tampering
- Provides NEMA rated protection

Application

Carpeted Space, High Density, Indoor Wi-Fi, Outdoor Wi-Fi, Stadium

General

Catalog Number	ATS-00416
Color	Light Grey
Compatibility	• Arista C-230 • Arista C-230E • Arista C-330 • Arista C-360 • Arista C-460 • Arista C-460E • Arista O-105E • Arista O-235 • Arista O-235E • Aruba/HP AP-504 • Aruba/HP AP-505 • Aruba/HP AP-514 • Aruba/HP AP-515 • Aruba/HP AP-518 • Aruba/HP AP-534 • Aruba/HP AP-535 • Aruba/HP AP-555 • Aruba/HP AP-565 • Aruba/HP AP-567 • Aruba/HP AP-574 • Aruba/HP AP-615 • Aruba/HP AP-634 • Aruba/HP AP-635 • Aruba/HP AP-654 • Aruba/HP AP-655

- Aruba/HP AP-734
- Aruba/HP AP-735
- Aruba/HP AP-754
- Aruba/HP AP-755
- Cisco Catalyst 9105AXI
- Cisco Catalyst 9115i
- Cisco Catalyst 9115e
- Cisco Catalyst 9117
- Cisco Catalyst 9120AXI
- Cisco Catalyst 9120AXE
- Cisco Catalyst 9120AXP
- Cisco Catalyst 9124AXD
- Cisco Catalyst 9124AXE
- Cisco Catalyst 9124AXI
- Cisco Catalyst 9130AXE
- Cisco Catalyst 9130AXI
- Cisco Catalyst 9136i
- Cisco CW9162
- Cisco CW9163E
- Cisco CW9164
- Cisco CW9166
- Cisco IW9167E
- Cisco MR46
- Cisco MR46E
- Cisco MR56
- Cisco MR56E
- Cisco MR57
- Cisco MR76
- Cisco MR86
- Mist AP24
- Mist AP32
- Mist AP32e
- Mist AP33
- Mist AP43
- Mist AP43e
- Mist AP45
- Mist AP45E
- Mist AP47E

	• Mist AP63 • Mist AP63E • Mist AP64
Cord Grip	No
Door Type	Solid
Enclosure Style	Mounting Feet
Indoor/Outdoor	Indoor or Outdoor
Installation Type	Blank Backplate
Lock Type	Key
Material	Polycarbonate
Operating Temperature	-28 to 115 °C
Technology	802.11ac, 802.11n, 802.3af, 802.3at
UPC	662620433769

Dimensions

Dimensions	24 in x 24 in x 10 in
Height	10 in
Length	24 in
Width	24 in

Certifications And Compliance

Ratings	122
---------	-----

Product Assets

- [Sales Drawings - Outline Drawing](#)
- [Specifications - Specification Sheet](#)

