



# Universal AP All-Thread Drop Mount

By AccelTex Solutions  
Catalog # [ATS-00716](#)



ATS-00716 (former catalog number ATS-DRPMNT-UNIV1). The AccelTex Solutions Universal All-Thread Drop Mount provides a unique solution to mount a Cisco, Aruba or other T-Bar mounted AP using All-Thread. The AP snaps into place by fitting the AP mounting feet into pre-defined keyholes in the mount or using the T-Bar mount supplied with the AP. This mount can be used to lower the height of the antenna and AP in a building with high ceilings or can even be placed above a suspended ceiling. All-Thread and fasteners not included.

## Features

- All-Thread drop mount for T-Bar mounted APs
- Suitable for high ceilings or above suspended ceiling installations
- AP snaps securely into place with pre-defined keyholes or T-Bar mount

## Application

Indoor Wi-Fi

## General

Catalog Number	ATS-00716
Color	White
Compatibility	<ul style="list-style-type: none"><li>• Arista C-230</li><li>• Arista C-330</li><li>• Arista C-360</li><li>• Arista C-460</li><li>• Aruba/HP AP-515</li><li>• Aruba/HP AP-535</li><li>• Aruba/HP AP-555</li><li>• Aruba/HP AP-565</li><li>• Aruba/HP AP-567</li><li>• Aruba/HP AP-575</li><li>• Aruba/HP AP-615</li><li>• Aruba/HP AP-635</li><li>• Aruba/HP AP-655</li><li>• Aruba/HP AP-735</li><li>• Aruba/HP AP-755</li><li>• Cisco Catalyst 9115i</li><li>• Cisco Catalyst 9117</li><li>• Cisco Catalyst 9120AXE</li><li>• Cisco Catalyst 9120AXI</li><li>• Cisco Catalyst 9124AXE</li><li>• Cisco Catalyst 9124AXI</li><li>• Cisco Catalyst 9130AXE</li><li>• Cisco Catalyst 9130AXI</li></ul>

- Cisco Catalyst 9136i
  - Cisco CW9162
  - Cisco CW9163E
  - Cisco CW9164
  - Cisco CW9166
  - Cisco IW9165
  - Cisco IW9165E
  - Cisco IW9167E
  - Cisco MR46
  - Cisco MR56
  - Cisco MR57
  - Cisco MR76
  - Cisco MR86
  - Mist AP33
  - Mist AP32
  - Mist AP43
  - Mist AP34
  - Mist AP24
  - Mist AP45
  - Mist AP47
  - Mist AP47D
- Indoor  
3/8" All Thread or Beam Clamp  
Steel  
802.11ac, 802.11ax, 802.11n  
662620434889

Indoor/Outdoor  
Installation Type  
Material  
Technology  
UPC

## Dimensions

Dimensions	7.3 in x 7.1 in x 4.3 in
Height	4.3 in
Length	7.3 in
Width	7.1 in

## Product Assets

- [Sales Drawings - Outline Drawing](#)
- [Specifications - Specification Sheet](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved  
ATS-ATS00716-SPEC-EN | REV 4/2025