



11.75" x 11.75" x 4" Black ABS AP Cover

By AccelTex Solutions
Catalog # [ATS-03292](#)

ATS-03292 (former catalog number ATS-COV-11751175-BLK-ABS). The AccelTex Solutions AP Cover provides an opaque wall or ceiling mount option to protect and conceal enterprise-class APs from environmental threats and tampering. Developed for enterprise applications, this aesthetically pleasing enclosure is inconspicuous in most indoor environments.

Features

- Made with durable ABS material
- Black color
- Conceals enterprise-class APs
- Protects enterprise-class APs

Application

Indoors

General

Catalog Number
Color
Compatibility

ATS-03292
Black

- Aruba/HP AP303
- Aruba/HP AP314
- Aruba/HP AP315
- Aruba/HP AP334
- Aruba/HP AP335
- Aruba/HP AP504
- Aruba/HP AP505
- Aruba/HP AP514
- Aruba/HP AP515
- Aruba/HP AP518
- Aruba/HP AP534
- Aruba/HP AP535
- Aruba/HP AP555
- Aruba/HP AP615
- Aruba/HP AP635
- Aruba/HP AP655
- Aruba/HP AP735
- Aruba/HP AP755
- Cisco 9136I
- Cisco 9162I
- Cisco 9164I
- Cisco 9166I
- Cisco 9130AXE
- Cisco 9130AXI
- Cisco 9124AXE
- Cisco 9124AXI
- Cisco 9124AXD



- Cisco 9120AXE
- Cisco 9120AXI
- Cisco 9115AXE
- Cisco 9115AXI
- Cisco 9117AXI
- Cisco 9105AXI
- Cisco 3802I
- Cisco 3802E
- Meraki MR36
- Meraki MR57
- Meraki MR52
- Meraki MR53E
- Meraki MR42E
- Meraki MR72
- Meraki MR74
- Mist AP47
- Mist AP47E
- Mist AP47D
- Mist AP45
- Mist AP45E
- Mist AP34
- Mist AP24
- Mist AP63E
- Mist AP63
- Mist AP43E
- Mist AP43
- Mist AP41E
- Mist AP41
- Mist AP33
- Mist AP32E
- Mist AP32
- Arista C-360
- Arista C-330
- Arista C-460
- Arista C460E
- Arista O-435
- Arista O-435E
- Arista O-235
- Arista O-235E
- Arista C-230
- Arista C-230E

Material
UPC

- Extreme AP305C
 - Extreme AP510i
 - Extreme AP505i
 - Extreme AP5010
- ABS
662620440484

Height 4 in
Length 11.75 in
Weight 0.7 lb
WeightMetric 0.318 kg
Width 11.75 in

Dimensions

Dimensions 11.75 in x 11.75 in x 4 in

Product Assets

[Specifications - BLACK ABS AP COVER ATS-COV-117511754-
BLK-ABS ATS-03292](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
ATS-ATS03292-SPEC-EN | REV 10/2024