



1PBS1/0, UV Rated Black Splicer/Reducer, 2 #14-1/0 kcmil

By Burndy
Catalog # 1PBS1/0



UV Rated Black UNITAP™, 2, #14 - 1/0 Kcmil, 2.91 in L, 0.91 in W.

Features

- UV Rated Covering over AL6061-T6 aluminum body saves time, lowering installation costs and eliminates taping
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces the number of connectors necessary to carry in inventory

Application

For Indoor Use Only, Copper Or Stranded Aluminum

General

Connector Type	Multi Tap
EU RoHS Indicator	Yes
Hex Key	3/16
Installation Torque Recommended in-lb	120 in-lb
Insulation	Y
Insulation Type	Plastisol
Material	Aluminum
Material - Hardware	Aluminum
Number Of Ports	2
Physical Attribute - Number of Screws	2
Plated	N
Plating Type	Unplated
Sub Brand	UNITAP
Temperature Rating	194° F
Trade Name	UNITAP™
Type	BIBS, Multi-Port
UPC	781810295922
UPC 12 Digit	7818102959222

Dimensions

Dimension - Height fraction	1.375 in
Dimension - Height inch	1.38 in
Dimension - L Length Overall mm	74 mm
Dimension - Length Overall inch	2.91 in
Dimension - Screw Size inch	7/16
Dimension - Width fraction	91/100 in
Dimension - Width inch	0.91 in
Dimension - Width mm	23 mm

Electrical Ratings

Voltage - Maximum 600 V

Conductor Related

Conductor - AL Str Size	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0
Conductor - AL Str Size Range	14 AWG - 1/0 AWG
Conductor - Copper Str Size	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0
Conductor - Copper Str Size Range	14 AWG - 1/0 AWG
Conductor Size	14-1/0 AWG
Conductor Type	<ul style="list-style-type: none">• AL C Str-Size• CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity 1

Product Assets

[Catalogs - UNITAP™ Products](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_PBS_LineArt](#)
[Sales Drawings - SD214514-03](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-1PBS1/O-SPEC-EN | REV 5/2024