



1PBS350, UV Rated Black Splicer/Reducer, 2, #10-350 kcmil

By Burndy
Catalog # 1PBS350



UV Rated Black UNITAP™, 2, #10 - 350 Kcmil, 4.63 in L, 1.34 in W.

Features

- UV Rated Covering over AL6061-T6 aluminum body saves time, lowering installation costs and eliminates taping
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces the number of connectors necessary to carry in inventory

Application

For Indoor Use Only, Copper Or Stranded Aluminum

General

Catalog Number	1PBS350
Connector Type	Multi Tap
EU RoHS Indicator	Yes
Hex Key	5/16
Installation Torque Recommended in-lb	275
Insulation	Y
Insulation Type	Plastisol
Material	Aluminum
Material - Hardware	Aluminum
Number Of Ports	2
Physical Attribute - Number of Screws	2
Plated	N
Plating Type	Unplated
Sub Brand	UNITAP
Temperature Rating	194° F
Trade Name	UNITAP™
Type	BIBS, Multi-Port
UPC	781810295908
UPC 12 Digit	7818102959088

Dimensions

Dimension - Height inch	2.35 in
Dimension - L Length Overall mm	118 mm
Dimension - Length Overall inch	4.63 in
Dimension - Screw Size inch	5/16
Dimension - Width fraction	1-17/50 in
Dimension - Width inch	1.34 in
Dimension - Width mm	34 mm

Electrical Ratings

Voltage - Maximum 600 V

Conductor Related

Conductor - AL Str Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil;350 kcmil
Conductor - AL Str Size Range	10 AWG - 350 kcmil
Conductor - Copper Str Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil;350 kcmil
Conductor - Copper Str Size Range	10 AWG - 350 kcmil
Conductor Size	10 AWG-350 KCMIL
Conductor Type	<ul style="list-style-type: none">• AL C Str-Size• CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity 1

Product Assets

[Catalogs - UNITAP™ Products](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section A - Mechanical](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_PBS_LineArt](#)
[Sales Drawings - SD214514-03](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-1PBS350-SPEC-EN | REV 6/2024