



BA16E8, Vinyl Ring Terminal For 22 - 16 AWG

By Burndy
Catalog # [BA16E8](#)



Vinyl Ring Terminal For 22 - 16 AWG.

Features

- Expanded insulation support accepts standard and large wire diameters providing lower inventory requirements and greater flexibility
- Funnel entry for easy wire insertion
- Manufactured of pure electrolytic copper to provide maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Deep V groove serration in the inner barrel for added holding strength and better conductivity
- Electro-tin plating for durable, long-lasting corrosion resistance
- 600 Volts maximum, 105°C maximum

Application

For Commercial, Light Duty Industrial Control and Power Circuit Applications

General

Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	VINYLUG
Trade Name	VINYLUG™
Type	Ring Tongue
UPC	781810026694
UPC 12 Digit	7818100266944

Dimensions

Dimension - Bolt Size fraction	#8
Dimension - Hole Size fraction	8/47
Dimension - Hole Size inch	0.17 in
Dimension - Length Overall inch	0.85 in
Dimension - Pad Width inch	0.31 in
Dimension - Stud Size inch	#8
Dimension - Z inch	0.26 in

Conductor Related

Conductor - Copper Solid Size Range	20 AWG -22 AWG; 16 AWG -18 AWG
Conductor - Copper Str Size Range	20 AWG -22 AWG; 16 AWG -18 AWG
Conductor Size	22 - 16 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1000
Minimum Pack Quantity	1000
Pallet Quantity	99999

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50093722](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-BA16E8-SPEC-EN | REV 1/2024