



BA16EL6, Vinyl Locking Fork Terminal For 22 - 16 AWG

By Burndy
Catalog # [BA16EL6](#)

Vinyl Locking Fork Terminal For 22 - 16 AWG.



Features

- Locking Fork Tongue design
- Allows for fast installation, screw only has to be loosened for termination
- Internal configuration of the fork prevents the terminal from coming off the screw without applying a pulling force
- Locking form is made from copper alloy and permits many installations while maintaining proper spring retention of forks

Application

For Fast Installation And Security

General

Catalog Number	BA16EL6
Connector Type	Locking Fork Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Locking Fork
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	VINYLUG
Trade Name	VINYLUG™
Type	BA-EL, Locking
UPC	781810026946
UPC 12 Digit	7818100269466

Dimensions

Dimension - Bolt Size fraction	#6
Dimension - Hole Size fraction	7/50
Dimension - Hole Size inch	0.14 in
Dimension - Length Overall inch	0.87 in
Dimension - Pad Width inch	0.28 in
Dimension - Stud Size inch	#6
Dimension - Z (inch)	0.23 in

Conductor Related

Conductor - Copper Solid Size Range	20 AWG -22 AWG; 16 AWG -18 AWG
Conductor - Copper Str Size Range	20 AWG - 22 AWG; 16 AWG - 18 AWG
Conductor Size	22 - 16 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1000
Minimum Pack Quantity	1000
Pallet Quantity	99999

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_BA14EL10_LineArt](#)
[Sales Drawings - 50094176](#)
[Specifications - BA16EL6](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-BA16EL6-SPEC-EN | REV 8/2024