



## BDBLCS4T3FS, 3-Pole Flex Rated Finger-Safe Power Distribution Block

By Burndy  
Catalog # [BDBLCS4T3FS](#)



POWER DISTRIBUTION BLOCKS.

### General

|                    |                          |
|--------------------|--------------------------|
| Catalog Number     | BDBLCS4T3FS              |
| Connector Type     | Power Distribution Block |
| Insulation         | Y                        |
| Material           | Aluminum                 |
| Number Of Poles    | 3                        |
| Plated             | Y                        |
| Plating Type       | Tin                      |
| Temperature Rating | 194° F                   |
| Trade Name         | VERSIPOLE™               |
| UPC                | 781810676929             |
| UPC 12 Digit       | 7818106769299            |

### Dimensions

|                                 |      |
|---------------------------------|------|
| Dimension - Height inch         | 4.15 |
| Dimension - L Length Overall mm | 231  |
| Dimension - Length Overall inch | 9.09 |

### Electrical Ratings

|                          |       |
|--------------------------|-------|
| Amperage Rating          | 620 A |
| Rating - Minimum Voltage | 600   |
| Voltage - Maximum        | 600 V |

### Conductor Related

|                                  |   |
|----------------------------------|---|
| Conductor - AL Str Run Range     | 6 AWG - 350 kcmil   |
| Conductor - AL Str Tap Range     | 6 AWG - 350 kcmil   |
| Conductor - Copper Str Run Range | 6 AWG - 350 kcmil   |
| Conductor - Copper Str Tap Range | 6 AWG - 350 kcmil   |
| Conductor Type                   | <ul style="list-style-type: none"><li>• AL C Str-Run</li><li>• CU C Str-Run</li><li>• AL C Str-Tap</li><li>• CU C Str-Tap</li></ul> |

### Certifications And Compliance

|                                    |     |
|------------------------------------|-----|
| Certification - CSA Approved       | No  |
| Certification - cULus              | Yes |
| Standards - RoHS Compliance Status | CM  |

### Logistics

|                       |     |
|-----------------------|-----|
| Carton Quantity       | 2   |
| Minimum Pack Quantity | 1   |
| Pallet Quantity       | 144 |

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50059695](#)  
[Specifications - BDBLCS4T3FS](#)