

BIBS2/03, Single Sided Three Conductor Clear Insulated Multi-Tap Connector

By Burndy
Catalog # [BIBS2/03](#)



Aluminum Multiple Tap Connector, Clear Insulated, 3 Port, 1 Sided Entry, 14-2/0 AWG, Al/Cu Rated.

Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory

General

Application	For Indoor Use Only, Copper Or Stranded Aluminum
Catalog Number	BIBS2/03
Connector Type	Multi Tap
EU RoHS Indicator	Yes
Hex Key	3/16
Insulation	Y
Insulation Type	Plastisol
Material	Aluminum
Material - Hardware	Aluminum
Number Of Ports	3
Physical Attribute - Number of Screws	3
Physical Attribute - Screw Type	Allen
Plated	N
Plating Type	Unplated
Sub Brand	UNITAP
Temperature Rating	194
Trade Name	UNITAP™
Type	BIBS, Multi-Port
UPC	781810223888
UPC 12 Digit	7818102238888

Dimensions

Dimension - Height fraction	1.375 in
Dimension - Height inch	1.38 in
Dimension - L Length Overall mm	56 mm
Dimension - Length Overall inch	2.19 in
Dimension - Width fraction	1-31/100 in
Dimension - Width inch	1.31 in
Dimension - Width mm	33 mm

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - AL Str Size	8 AWG;6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG
Conductor - AL Str Size Range	8 AWG-2/0 AWG
Conductor - Copper Str Size	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 Str
Conductor - Copper Str Size Range	14 AWG - 2/0 AWG
Conductor Size	14-2/0 AWG
Conductor Type	AL C Str-Size CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct	No
Burial	
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards	UL 486A-486B
Met	
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[3D Models - BIBS203_MODEL-IGES](#)
[3D Models - BIBS203_MODEL-PDF](#)
[3D Models - BIBS203_MODEL-STEP](#)
[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
[Catalogs - UNITAP™ Products](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_BIBS_Lineart](#)
[Sales Drawings - sc210991-11](#)