



BIBS2/06FXMT, Single Sided Mounted Flex Rated Six Conductor Clear Insulated Mult-Tap Connector



By Burndy
Catalog # [BIBS2/06FXMT](#)

Aluminum UNITAP, Mountable Single Sided Entry, #14-2/0 Class B & C, #14-#1 Class G,H,I,K, DLO, 6 PORT.

Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory
- Suitable for Code and Flex Conductor
- Color-coordinated conductor port caps display wire range and classes of conductor accepted
- Screw port caps show installation torque information for easy reference

General

Catalog Number	BIBS2/06FXMT
Color Code	Black
Connector Type	Multi Tap
Insulation	Y
Material	Aluminum
Number Of Ports	6
Plated	Y
Plating Type	Tin Plated Aluminum
Temperature Rating	135°C
Trade Name	UNITAP™
UPC	621945440302
UPC 12 Digit	6219454403022

Dimensions

Dimension - Height inch	1.38 in
Dimension - L Length Overall mm	134.57 mm
Dimension - Length Overall inch	5.298 in
Dimension - Width inch	1.31 in
Dimension - Width mm	33 mm

Electrical Ratings

Operating Voltage	600 V
-------------------	-------

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper DLO Size Range	14 - 1 Str
Conductor - Copper Flex G Size Range	14 - 1 Str
Conductor - Copper Flex H Size Range	14 - 1 Str
Conductor - Copper Flex I Size Range	14 - 1 Str
Conductor - Copper Flex K Size Range	14 - 1 Str
Conductor - Copper Str Size Range	14 AWG - 2/0 AWG
Conductor Size	14-2/0 AWG
Conductor Type	<ul style="list-style-type: none">• AL C Str-Size• CU C Str-Size• CU C Fex-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL467
Standards - Industry Standards	UL467
Met	
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - UNITAP™ Products](#)
- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50050187](#)
- [Specifications - BIBS2/06FXMT](#)
- [Specifications - BURNDY_BIBS206FXMT_Specsheet](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-BIBS206FXMT-SPEC-EN | REV 10/2024