



## **BIBS25014FX, Single Sided Flex Rated Fourteen Conductor Clear Insulated Mult-Tap Connector**

By Burndy  
Catalog # [BIBS25014FX](#)

Aluminum UNITAP, Single Sided Entry, #10-250 Class B & C ,#10-3/0 Class G,H,I,K, DLO, 14 PORT.



## Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory
- Suitable for Code and Flex Conductor
- Color-coordinated conductor port caps display wire range and classes of conductor accepted
- Screw port caps show installation torque information for easy reference

## General

Catalog Number	BIBS25014FX
Color Code	Yellow
Connector Type	Multi Tap
Insulation	Y
Material	Aluminum
Number Of Ports	14
Plated	Y
Plating Type	Tin Plated Aluminum
Temperature Rating	135°C
Trade Name	UNITAP™
UPC	621945439610
UPC 12 Digit	6219454396100

## Dimensions

Dimension - Height inch	2.13 in
Dimension - L Length Overall mm	331.22 mm
Dimension - Length Overall inch	13.04 in
Dimension - Width inch	2.13 in
Dimension - Width mm	54 mm

## Electrical Ratings

Operating Voltage	600 V
Voltage - Maximum	600 V

## Conductor Related

Conductor - Copper DLO Size	10 - 3/0 Str Range
Conductor - Copper Flex G Size	10 - 3/0 Str Range
Conductor - Copper Flex H Size	10 - 3/0 Str Range
Conductor - Copper Flex I Size	10 - 3/0 Str Range
Conductor - Copper Flex K Size	10 - 3/0 Str Range
Conductor - Copper Str Size	10 AWG - 250 kcmil Range
Conductor Size	10 AWG-250 KCMIL
Conductor Type	<ul style="list-style-type: none"><li>• AL C Str-Size</li><li>• CU C Str-Size</li><li>• CU C Fex-Size</li></ul>

## Certifications And Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards	UL 486A-486B
Met	
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

## Logistics

Minimum Pack Quantity	5
-----------------------	---

## Product Assets

- [Catalogs - UNITAP™ Products](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50046931](#)
- [Specifications - BIBS25014FX](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY-BIBS25014FX-SPEC-EN | REV 8/2024