



## **BIBS35010FXMT, Single Sided Mounted Flex Rated Ten Conductor Clear Insulated Mult-Tap Connector**

By Burndy  
Catalog # [BIBS35010FXMT](#)

Aluminum UNITAP, Mountable Single Sided Entry, #10-350 Class  
B & C, #10-250 Class G,H,I,K, DLO, 10 PORT.



## Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory
- Suitable for Code and Flex Conductor
- Color-coordinated conductor port caps display wire range and classes of conductor accepted
- Screw port caps show installation torque information for easy reference

## General

Catalog Number	BIBS35010FXMT
Color Code	Red
Connector Type	Multi Tap
Insulation	Y
Material	Aluminum
Number Of Ports	10
Plated	Y
Plating Type	Tin Plated Aluminum
Temperature Rating	135°C
Trade Name	UNITAP™
UPC	621945440371
UPC 12 Digit	6219454403711

## Dimensions

Dimension - Height inch	2.5 in
Dimension - L Length Overall mm	281.18 mm
Dimension - Length Overall inch	11.07 in
Dimension - Width inch	2.25 in
Dimension - Width mm	57 mm

## Electrical Ratings

Operating Voltage	600 V
Voltage - Maximum	600 V

## Conductor Related

Conductor - Copper DLO Size	10 - 250 Str Range
Conductor - Copper Flex G Size	10 - 250 Str Range
Conductor - Copper Flex H Size	10 - 250 Str Range
Conductor - Copper Flex I Size	10 - 250 Str Range
Conductor - Copper Flex K Size	10 - 250 Str Range
Conductor - Copper Str Size	10 AWG - 350 kcmil Range
Conductor Size	10 AWG-350 KCMIL
Conductor Type	<ul style="list-style-type: none"><li>• AL C Str-Size</li><li>• CU C Str-Size</li><li>• CU C Fex-Size</li></ul>

## Certifications And Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL467
Standards - Industry Standards	UL467
Met	
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

## Logistics

Minimum Pack Quantity	5
-----------------------	---

## Product Assets

[Catalogs - UNITAP™ Products](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50050187](#)  
[Specifications - BIBS35010FXMT](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY-BIBS35010FXMT-SPEC-EN | REV 8/2024