



BIBS60012FXMT, Single Sided Mounted Flex Rated Twelve Conductor Clear Insulated Mult-Tap Connector

By Burndy

Catalog # [BIBS60012FXMT](#)

Aluminum UNITAP, Mountable Single Sided Entry, #4-600 Class
B & C ,#4-373 Class G,H,I,K, DLO, 12 PORT.



Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory
- Suitable for Code and Flex Conductor
- Color-coordinated conductor port caps display wire range and classes of conductor accepted
- Screw port caps show installation torque information for easy reference

General

Catalog Number	BIBS60012FXMT
Color Code	Green
Connector Type	Multi Tap
Insulation	Y
Material	Aluminum
Number Of Ports	12
Plated	Y
Plating Type	Tin Plated Aluminum
Temperature Rating	135°C
Trade Name	UNITAP™
UPC	621945440425
UPC 12 Digit	6219454404255

Dimensions

Dimension - Height inch	2.75 in
Dimension - L Length Overall mm	453.14 mm
Dimension - Length Overall inch	17.84 in
Dimension - Width inch	2.13 in
Dimension - Width mm	54 mm

Electrical Ratings

Operating Voltage	600 V
Voltage - Maximum	600 V

Conductor Related

Conductor - Copper DLO Size	4 - 373 Str Range
Conductor - Copper Flex G Size	4 - 373 Str Range
Conductor - Copper Flex H Size	4 - 373 Str Range
Conductor - Copper Flex I Size	4 - 373 Str Range
Conductor - Copper Flex K Size	4 - 373 Str Range
Conductor - Copper Str Size	4 AWG - 600 kcmil Range
Conductor Size	4 AWG-600 KCMIL
Conductor Type	<ul style="list-style-type: none">• AL C Str-Size• CU C Str-Size• CU C Flex-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Minimum Pack Quantity	5
-----------------------	---

Product Assets

[Catalogs - UNITAP™ Products](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50050187](#)
[Specifications - BIBS60012FXMT](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-BIBS60012FXMT-SPEC-EN | REV 8/2024