

# BIPC1/02, Insulating Piercing Connector - Discontinued

By Burndy  
Catalog # [BIPC1/02](#)



Discontinued - Please see suggested substitute: [BIPC1/010SC](#)  
Insulation Piercing Connector, 8-1/0 AWG (Run), 8-2 AWG (Tap), 600 V.

## General

Application	For Splicing And Tapping Aluminum And Copper Conductors
Catalog Number	BIPC1/02
Connector Type	Insulation Piercing
EU RoHS Indicator	Yes
Installation Torque	180 LBS/in
Recommended in-lb	
Insulation	Y
Material	Aluminum
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Hexagonal Bolt
Physical Attribute - Socket Size	1/2
Plated	N
Plating Type	Unplated
Sub Brand	INSULATION PIERCING CONNECTOR
Type	BIPC
UPC	781810128701
UPC 12 Digit	7818101287011

## Dimensions

Dimension - Bolt Size inch	0.31 in
Dimension - Height inch	2.00 in
Dimension - L Length Overall mm	39 mm
Dimension - Length Overall inch	1.53 in
Dimension - Width inch	1.53 in
Dimension - Width mm	39 mm

## Electrical Ratings

Rating - Minimum Voltage	600
Voltage - Maximum	600 V

## Conductor Related

Conductor - AL Str Run Range	8 AWG-1/0 AWG
Conductor - AL Str Tap Range	8 AWG-2 AWG
Conductor - Copper Str Run Range	8 AWG-1/0
Conductor - Copper Str Tap Range	8 AWG-2 AWG
Conductor Type	AL C Str-Run CU C Str-Run AL C Str-Tap CU C Str-Tap

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	12
Minimum Pack Quantity	1
Pallet Quantity	5568

## Product Assets

- [3D Models - BIPC102\\_MODEL-STEP](#)
- [3D Models - BIPC102\\_MODEL-IGES](#)
- [3D Models - BIPC102\\_MODEL-PDF](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_BIPC\\_LineArt](#)
- [Sales Drawings - SD210728-01\\_A](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY-BIPC102-SPEC-EN | REV 6/2024