

BISR1/OFX, Flex Rated Clear Insulated Splice Reducer

By Burndy
 Catalog # [BISR1/OFX](#)



Aluminum UNITAP, In-Line Splice Reducer, #14-1/0 Class B & C, #14-#1 Class G,H,I,K, DLO, 2 PORT

Features

- Type BISR-FX In-Line Splice/Reducers for Code and Flex conductor are listed to UL486A-B, CSA Certified to C22.2, No. 65, and AL9CU dual rated
- Range taking designs reduce inventory needs
- Screw Port and Conductor Port caps provide protection against contamination and accidental contact of energized parts
- Caps are color coordinated to quickly identify maximum conductor size
- Screw Port caps display recommended installation torque values for quick and easy reference
- Conductor Port caps show accommodated wire range and class

General

Application	Tap connections and in-line splice/reductions are made quickly and easily with the UNITAP™ line of connectors
Catalog Number	BISR1/OFX
Color Code	Pink
Connector Type	In-Line
EU RoHS Indicator	Yes
Hex Key	3/16 in
Installation Torque	120 in-lb
Recommended in-lb	
Insulation	Y
Material	Aluminum
Number Of Ports	2
Plated	Y
Plating Type	Tin Plated Aluminum
Sub Brand	UNITAP
Temperature Rating	135°C
Trade Name	UNITAP™
Type	BISR,Multi-Port
UPC	621945439979
UPC 12 Digit	6219454399799

Dimensions

Dimension - Height inch	1.38 in
Dimension - L Length Overall mm	73.92 mm
Dimension - Length Overall inch	2.91 in
Dimension - Width inch	0.91 in
Dimension - Width mm	23 mm

Electrical Ratings

Operating Voltage	600 V
Voltage - Maximum	600 V

Conductor Related

Conductor - Copper DLO Size Range	14 - 1 Str
Conductor - Copper Flex G Size Range	14 - 1 Str
Conductor - Copper Flex H Size Range	14 - 1 Str
Conductor - Copper Flex I Size Range	14 - 1 Str
Conductor - Copper Flex K Size Range	14 - 1 Str
Conductor - Copper Str Size Range	14 AWG - 1/0 AWG
Conductor Size	14-1/0 AWG
Conductor Type	AL C Str-Size
	CU C Str-Size
	CU C Fex-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity 1

Product Assets

[Catalogs - UNITAP™ Products](#)

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)

[Customer Notices - Prop 65 Notice](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Sales Drawings - 50046931](#)



A Hubbell brand